

ÖLFLEX® CHAIN 819 CP

PVC

ÖLFLEX® CHAIN 819 CP - PVC

PU-

- 가
UL/cUL



가
, 가

ÖLFLEX® CHAIN 819 CP

EMC-

Indoor applications or dry rooms

IEC/EN: 60332-1-2
UL/CSA: , FT2

EMC-

: UL AWM Style 21576
: cUL AWM Style I/II A FT2
UL File No. E63634
: 가 T3

: PVC

Lapp-PU-Special Blend (, RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

Black with white numbers acc. to VDE 0293-334

VDE 0295 5/ IEC 60228 5
가 가

Flexing: up from 10 x outer diameter
: 4 x

IEC U0/U: 300/500 V
UL: 1,000V

Core/core: 4000 V
Core/screen: 2000 V

G = GN/YE
X = GN/YE

: -5°C ~ +70°C (UL: +80°C)
: -40°C ~ +70°C(UL: +80°C)

A2-1

(23.04.2024)



ÖLFLEX® CHAIN 819 CP

www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
가 VAT 가 가 .

(23.04.2024)

ÖLFLEX® CHAIN 819 CP

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1027900	2 X 0.5	5.8	22.5	42.9
1027901	3 G 0.5	6.1	27.1	50.6
1027902	4 G 0.5	6.6	35.1	62.6
1027903	5 G 0.5	7.1	43.1	74.7
1027904	7 G 0.5	8.5	55.8	101
1027905	12 G 0.5	10	83.1	144.5
1027906	18 G 0.5	11.8	120	207.1
1027907	25 G 0.5	14.1	171	288.6
1027910	2 X 0.75	6.2	30.4	52.7
1027911	3 G 0.75	6.6	37.5	63.4
1027912	4 G 0.75	7.1	47.9	78
1027913	5 G 0.75	7.7	55.2	90.4
1027914	7 G 0.75	9.1	75.9	126.1
1027915	12 G 0.75	10.9	115.3	183.6
1027916	18 G 0.75	13	168	269.8
1027917	25 G 0.75	15.6	239.6	377
1027920	2 X 1.0	6.5	35.3	58.5
1027921	3 G 1.0	6.9	44.7	71.6
1027922	4 G 1.0	7.5	57.7	89.4
1027923	5 G 1.0	8.3	70.3	110.2
1027924	7 G 1.0	9.8	92.7	149.2
1027925	12 G 1.0	11.7	148.7	224.4
1027926	18 G 1.0	14	224.1	331.3
1027927	25 G 1.0	16.7	299.5	449.2
1027930	2 X 1.5	7.1	47.9	73.8
1027931	3 G 1.5	7.5	62.5	92.6
1027932	4 G 1.5	8.4	80	118.9
1027933	5 G 1.5	9.1	97.5	142.7
1027934	7 G 1.5	10.9	129.7	194.9
1027935	12 G 1.5	13.3	211	301.9
1027936	18 G 1.5	15.7	319	447.8
1027937	25 G 1.5	18.7	428.1	606.5
1027940	3 G 2.5	9	97.4	138.9
1027941	4 G 2.5	10.1	124.8	178.2

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CHAIN 819 CP

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1027944	5 G 2.5	11.2	148.7	215.4
1027942	7 G 2.5	13.5	206.5	301.6
1027943	12 G 2.5	16.2	347.5	478.5
1027950	4 G 4.0	11.9	187	256.1
1027952	4 G 10.0	18.2	452.1	606.5
1027955	4 G 16.0	21.3	699.5	884.2
1027957	4 G 25.0	26.3	1,062.1	1,349.7

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16