

# ÖLFLEX® CHAIN 90 P

PUR

ÖLFLEX® CHAIN 90 CP - UL/cUL AWM

- 가



(23.12.2023)

# ÖLFLEX® CHAIN 90 P

PUR  
가 , 가  
,  
가

가 가  
가

가 가

- VDE 0472-815
  - IEC 60332-1-2 UL/cUL VW-1, FT1
  - IEC 60332-3-24 Cat. C /-25 Cat. D
- , UV

DNV GL approved  
UL File No. E63634  
: UL AWM Style 11624, VW-1  
: cUL AWM I/II A, FT1  
: 가 T3

(class 6)  
: TPE  
, (RAL 9005 )

ETIM 5: ETIM 5.0 Class-ID: EC000057  
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000057  
ETIM 6.0 Class :  
- , 가  
: VDE 0295 class 6, IEC 60228 class 6 가

WTG : TW-0 & TW-2, T0  
:  
: 7.5 x  
: 3 x

# ÖLFLEX® CHAIN 90 P

: IEC: U<sub>0</sub>/U 600/1000 V  
UL & CSA: 1000 V  
: 4000 V  
: : -35°C ~ +80°C  
: -50°C +80°C  
: A2-1

www.lappkabel.de/en/cable-standradlengths ( : ) 가  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

	(mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
ÖLFLEX® CHAIN 90 P					
1026513	1.5	6.3	-	14.4	48
1026514	1.5	6.3		14.4	48
1026515	2.5	6.9	-	24	63
1026516	2.5	6.9		24	63
1026517	4	7.2	-	38.4	77
1026518	4	7.2		38.4	77
1026519	6	7.7	-	57.6	95
1026520	6	7.7		57.6	95
1026521	10	9.1	-	96	145
1026522	10	9.1		96	145
1026523	16	10.6	-	153.6	205
1026524	16	10.6		153.6	205
1026525	25	12.3	-	240	290
1026526	25	12.3		240	290
1026527	35	13.3	-	336	413
1026528	35	13.3		336	413
1026529	50	15.9	-	480	535
1026530	50	15.9		480	535
1026531	70	18	-	672	776
1026532	70	18		672	776
1026533	95	19.9	-	912	998
1026534	95	19.9		912	998
1026535	120	22.5	-	1152	1249
1026536	120	22.5		1152	1249
1026537	150	24.6	-	1440	1486
1026538	150	24.6		1440	1486
1026539	185	27.2	-	1776	1788
1026540	185	27.2		1776	1788
1026541	240	32.1	-	2304	2381
1026542	240	32.1		2304	2381
1026543	300	34	-	2880	2964
1026544	300	34		2880	2964