

H07ZZ-F

, ; : , 가

H07ZZ-F, <HAR>, power and control cable, rubber, 450/750V, halogen-free, flame-retardant IEC 60332-3-24 bundle fire test, low smoke LSOH EN 61034-2



VDE 0100-711 ,
<HAR> -
가

CENELEC ,

가

가
"<HAR>"

EN 50565-2 :
가

가
IEC 60332-1-2 IEC 60332-3-24
IEC 61034 , /
EN 50363-6, EN 60811-403, EN 50396-8.1.3

(21.02.2024)

H07ZZ-F

EN 50525-3-21 <HAR> H07ZZ-F

: ,

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

: 5 : VDE 0293-308 . T9

6 :

: VDE 0295 5/ IEC 60228 5

가 가

: 4 ~ 8 x (EN 50565-1)

: U0/U: 450/750 VAC

: :

U0/U: 600/1000 V

: 2500 V

: G = GN/YE

X = GN/YE

: VDE 0298 4

EN 50565-1/ VDE 0298-565-1

: Fixed installation: -40°C up to +90°C

Occasionally moved: -5°C up to +90°C

: , 가 가 . (.) 가 .

www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1600810	3 G 1.5	9.2 - 10.8	43.2	125
1600811	4 G 1.5	10.2 - 11.8	57.6	155
1600812	5 G 1.5	11.2 - 12.8	72	190
1600815	14 G 1.5	18.8 - 21.3	201.6	570
1600816	18 G 1.5	20.7 - 23.3	259.2	750
1600820	3 G 2.5	10.9 - 12.5	72	185
1600821	4 G 2.5	12.1 - 13.9	96	235
1600822	5 G 2.5	13.3 - 15.1	120	290
1600823	7 G 2.5	17.1 - 19.3	168	520
1600825	14 G 2.5	22.2 - 25	336	860
1600836	4 G 4.0	14.0 - 16.0	153.6	325
1600837	5 G 4.0	15.6 - 17.6	192	410
1600841	4 G 6.0	15.7 - 17.7	230.4	440
1600842	5 G 6.0	17.5 - 19.5	288	550
1600844	4 G 10.0	20.9 - 23.3	384	770
1600845	5 G 10.0	22.9 - 25.7	480	950
1600847	4 G 16.0	23.8 - 26.4	614.4	1070
1600849	4 G 25.0	28.9 - 32.1	960	1570
1600851	4 G 35.0	32.5 - 36.1	1344	2040
1600852	4 G 50.0	37.7 - 41.5	1920	2810

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16