

NSSHÖU

NSSHÖU, VDE, / , 0,6/1 kV, class 5, -25°C ~ +90°C, ,



(23.04.2024)

NSSHÖU

IEC 60332-1-2
EN 60811-404

VDE 0250-812 <VDE> NSSHOU

: 3GI3
: , GM1b 5GM5
: , 5GM5

ETIM 5:

ETIM 5.0 Class-ID: EC000057
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057
ETIM 6.0 Class :

: 5 : VDE 0293-308 . T9
6 :

: VDE 0295 5/ IEC 60228 5
가 가

: : 10 x
: 5 x

: U0/U: 600/1000 V

: 3000 V

: G = GN/YE

: X = GN/YE

: VDE 0298 Part 4, 15

: Occasionally moved: -25°C up to +90°C
: -40°C ~ +90°C

: 30 kg or 250 m, 가 가 (.) 가 .
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
NSSHÖU-O				
1600500	1 X 16.0	10.9	153.6	260
1600501	1 X 25.0	13.3	240	390
1600502	1 X 35.0	14.4	336	500
1600503	1 X 50.0	16.7	480	680
1600504	1 X 70.0	18.9	672	900
1600505	1 X 95.0	21.0	912	1150
1600506	1 X 120.0	23.3	1152	1440
1600507	1 X 150.0	25.2	1440	1750
1600508	1 X 185.0	28.4	1776	2180
1600509	1 X 240.0	31.4	2304	2790
NSSHÖU-J				
1600516	3 G 1.5	11.8	43.2	200
16005243	4 G 1.5	12.7	57.6	230
16005333	5 G 1.5	13.6	72	280
1600517	3 G 2.5	13.2	72	260
16005253	4 G 2.5	15.4	96	360
16005343	5 G 2.5	16.5	120	420
1600541	7 G 2.5	20.0	168	600
1600544	12 G 2.5	26.0	288	860
16005263	4 G 4.0	16.9	153.6	470
16005353	5 G 4.0	18.2	192	550
16005273	4 G 6.0	18.3	230.4	580
16005363	5 G 6.0	20.6	288	740
16005283	4 G 10.0	22.3	384	950
16005373	5 G 10.0	24.1	480	1100
16005293	4 G 16.0	26.1	614	1400
16005383	5 G 16.0	28.3	768	1720
16005303	4 G 25.0	31.2	960	2000
16005313	4 G 35.0	34.1	1344	2700
16005323	4 G 50.0	41.0	1920	3700