

ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

가



Lapp



가

Lapp

(19.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

For travel distances up to 10 m

PVC

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

:  
:  
:  
:  
:  
:  
:  
:  
:  
:

: V / L2  
: WS; SW  
: W/L3/D/L-GN/YE  
IEC 60228/VDE 0295 class 5  
Chain application: 7,5 x cable diameter  
: 4 x  
:  
U0/U: 600/1000 V  
UL & CSA: 1000 V  
Core/Core: 4 kV  
Core/Screen: 4 kV  
G = GN/YE  
Chain application: -5°C to +70°C (UL: +80°C)  
: -40°C bis +80°C  
5 mio. cycles

, 가 가 ( . ) 가 .  
가

가 VAT 가 가 .

Bendingradius: Resolvercable 15x Outerdiameter

Resolver Corecode acc. DIN 47100

Allen Bradley / Rockwell part designations are registered trademarks of Allen Bradley / Rockwell , and are listed for comparison purposes only

(19.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

	(m)	LENZE®	OD in mm	(CORE) / (mm <sup>2</sup> )	kg/1.000 pieces
5490000061	10.0	2090-CPBM7E7-16AA	12.7	4G1,5+(2x1,5)	1,441.27

(19.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16