

ÖLFLEX® SERVO FD 796 P

PUR

ÖLFLEX® SERVO FD 796 P - UL/CSA AWM VDE 가

- 가
AWM

VDE



가 가 가

PUR

, ,
, 가

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® SERVO FD 796 P

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2

VDE - reg - no. 8591 (4G1,5)
UL AWM Style 20234
cULus AWM I/II A/B, 1000V 80° FT1
CSA AWM I/II A, 1000V 80° FT1
UL File No. E63634

: 가 T3

(class 6)
: (PP)
P/N : 1~2 (Pitch)
PUR , (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0
ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :
: U/L1/C/L+ ; V/L2; W/L3/D/L-;
GN/YE
: ,
2 : ; 5; 6; 7; 8
0,34mm² : / / /
: VDE 0295 class 6, IEC 60228 class 6 가
: : 7.5 x
: 4 x
: IEC U0/U: 600/1000 V
UL & CSA: 1000 V
: Core/Core: 4 kV
Core/Screen: 2 kV
: G = GN/YE

(22.07.2024)



ÖLFLEX® SERVO FD 796 P

:

: -40 ~ 90°C(UL/CSA: 80°C)

: -50 ~ 90°C(UL/CSA: 80°C)

:

A2-1

www.lappkabel.de/en/cable-standradlengths

(:) 가

가 VAT 가 가 .

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO FD 796 P

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SERVO FD 796 P				
0025319	4 G 1,5 + (2 x 1,5)	11.7	99	217
0025320	4 G 2,5 + (2 x 1,5)	13.1	134	270
0025321	4 G 4 + (2 x 1,5)	14.2	195	333
0025322	4 G 6 +(2 x 1,5)	16.0	272	403
0025323	4 G 10 + (2 x 1,5)	18.4	425	581
0025324	4 G 16 + (2 x 1,5)	22.1	656	887
0025326	4 G 0,75 + 2 x (2 x 0,34)	10.9	54	143
0025327	4 G 1,5 + 2 x (2 x 0,75)	12.3	103	209
0025328	4 G 2,5 + 2 x (2 x 1,0)	14.3	152	306
0025312	4 G 4 + 2 x (2 x 1,0)	15.4	218	381
0025329	4 G 4 + (2 x 1,0) + (2 x 1,5)	15.6	231	388
0025330	4 G 6 + (2 x 1,0) + (2 x 1,5)	17.1	308	460

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16