


# ÖLFLEX® SERVO FD 798 CP

PUR

ÖLFLEX® SERVO FD 798 CP - UL/CSA AWM 가

- 가

AWM



가

가

가

PUR

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® SERVO FD 798 CP

UL/CSA: VW-1, FT1.  
IEC/EN: 60332-1-2

UL AWM Style 20236  
CSA AWM IA/B; IIA/B FT 1  
UL File No. E63634

: 가 T3

: (PP) ( )

PUR , (RAL 6018)

ETIM 5: ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

: ÖLFLEX® SERVO FD 798 CP

:  
: : 7.5 x  
: 4 x

: IEC: 30 V  
UL & CSA: 30 V

: / : 1500 V  
Core/screen: 750 V rms

: : -40 ~ 90°C(UL/CSA: 80°C)  
: -50 ~ 90°C(UL/CSA: 80°C)

: A2-1

(22.07.2024)



# ÖLFLEX® SERVO FD 798 CP

, ( : ) 가  
 www.lappkabel.de/en/cable-standradlengths  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 DESINA - Decentralized and standardized installation technology for machine tools and manufacturing systems  
 가 VAT 가 가 .

# ÖLFLEX® SERVO FD 798 CP

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX®				
SERVO FD 798 CP				
0036910	(4x2x0,34+4x0,5)	8.9	79	125
0036949	(3x(2x0,14)+(2x(0,5)))	9.6	70	120
0036912	(3x(2x0,14)+4x0,14+2x0,5)	8.8	68	110
0036913	(3x(2x0,14)+4x0,14+2x0,5+4x0,22)	9.4	80	130
0036942	(2x2x0,18)	5.0	24	47
0036924	(4x2x0,18)	6.4	30	52
0036923	(8x2x0,18)	7.8	51	85
0036926	(12x0,22)	7.1	44	73
0036915	(4x2x0,25+2x1,0)	8.8	63	109
0036927	(4x2x0,25+2x0,5)	8.5	62	98
0036943	(4x1+4x2x0,14+(4x0,14))	9.7	103	175
0036944	(3x(2x0,25)+3x0,25+2x1,0))	9.3	96	162
0036929	(2x(2x0,25)+2x0,5)	8.7	46	98
0036930	(2x2x0,25+2x0,5)	7.3	38	72
0036914	(9x0,5)	8.8	71	110
0036946	3x(2x0,14)+(2x0,5)	10.0	68	142
0036941	3x(2x0,14)+(3x0,14)	9.2	57	125
0036945	4x(2x0,14)+2x(1)	11.4	92	115
0036916	(6x2x0,25+2x0,5)	10.3	67	121
0036917	(10x0,14+2x0,5)	7.7	41	82
0036918	(10x0,14+4x0,5)	8.1	54	98
0036928	(2x2x0,14+2x(2x0,14)+4x0,5+(4x0,14))	9.1	79	135
0036921	(4x2x0,25)	7.6	38	75
0036947	(5x2x0,25)	9.0	50	126
0036940	(6x2x0,25)	9.3	71	143
0036948	(5x2x22AWG)	8.7	75	109
0036920	(4x2x0,14+4x0,5)	8.2	51	95
0036911	(3x(2x0,14)+2x(0,5))	9.6	70	120
0036931	(3x(2x0,14)+2x(1))	9.1	74	137
0036932	(4x2x0,14+4x0,50+(4x0,14))	8.3	88	134
0036933	(3x2x0,25+2x0,5)	8.4	50	86

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® SERVO FD 798 CP

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
0036934	(5x2x0,25+2x0,5)	9.5	69	113
0036935	(3x2x24AWG)	6.5	36	70
0036936	(5x2x0,14+2x0,5)	7.8	51	101
0036937	(2x2x0,18+5x0,5)	7.6	62	110
0036938	(5x2x0,18+6x0,5)	8.7	79.2	113
0036939	(10x2x28AWG)	6.2	41	70

(22.07.2024)






©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® SERVO FD 798 CP



(22.07.2024)

# ÖLFLEX® SERVO FD 798 CP



(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16