

ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

가



Lapp



가

Lapp

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

For travel distances up to 10 m

PVC

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

:

U/L2/C/L +

: V / L2

: W/L3/D/L-GN/YE

: WS; SW

:

IEC 60228/VDE 0295 class 5

:

Chain application: 7,5 x cable diameter
: 4 x

:

U0/U: 600/1000 V
UL & CSA: 1000 V

:

Core/Core: 4 kV
Core/Screen: 4 kV

:

G = GN/YE

:

Chain application: -5°C to +70°C (UL: +80°C)
: -40°C bis +80°C

:

5 mio. cycles

, 가 가 (.) 가 .
가

가 VAT 가 가 .

Bendingradius: Resolvercable 15x Outerdiameter

Resolver Corecode acc. DIN 47100

Allen Bradley / Rockwell part designations are registered trademarks of Allen Bradley / Rockwell , and are listed for comparison purposes only

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO Core Line acc. Allen Bradley / Rockwell (PVC)

	(m)	LENZE®	OD in mm	(CORE) / (mm ²)	kg/1.000 pieces
5490000061	10.0	2090-CPBM7E7-16AA	12.7	4G1,5+(2x1,5)	1,441.27
5490000053	10.0	2090-CPBM7DF-16AA	12.7	4G1,5+(2x1,5)	1,441.27
5490000057	10.0	2090-CPWM7DF-16AA	8	4G1,5	818.1
5490000059	10.0	2090-CPWM7DF-14AA	11.1	4G2,5	1212

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16