

ÖLFLEX® SERVO Core Line für Siemens 6FX5002 (PVC)

가



Lapp



가

Lapp

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO Core Line für Siemens 6FX5002 (PVC)

For travel distances up to 10 m

PVC ,

SIEMENS®

1.5 mm² 가

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

:

: V / L2
U/L2/C/L +

: W/L3/D/L-GN/YE

: WS; SW

:

VDE 0295 5/ IEC 60228 5
가 가

:

Chain application: 7,5 x cable diameter
: 4 x

:

U0/U: 600/1000 V
UL & CSA: 1000 V

:

Core/Core: 4 kV
Core/Screen: 4 kV

:

G = GN/YE

:

Chain application: -5°C to +70°C (UL: +80°C)
: -40°C bis +80°C

:

5 mio. cycles

Siemens

(6FX5002/5008, 6FX7002/7008, 6FX8002/8008) Siemens AG

가

가 VAT 가 가

Further Article and length online <https://servoconfigurator.lappgroup.com/>

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO Core Line für Siemens 6FX5002 (PVC)

	(mm)	(m)	(CORE) / (mm ²)	SIEMENS®	kg/1.000 pieces		PU
ÖLFLEX® SERVO Core Line für Siemens 6FX5002 (PVC)							
5480007020	9.4	10.0	4 G 1,5	5CA05	818.1	가	1
5480007090	11.1	10.0	4 G 2,5	5CA15	1212	가	1
5480007510	9.4	10.0	4 G 1,5	5CN01	830.25	가	1
5480007650	11.1	10.0	4 G 2,5	5CN11	1230	가	1
5480007720	9.4	10.0	4 G 1,5	5CN21	830.25	가	1
5480007790	11.1	10.0	4 G 2,5	5CN31	1230	가	1
5480008210	11.1	10.0	4 G 2,5	5CQ15	1212	가	1
5480008630	9.4	10.0	4 G 1,5	5CS01	738.4	가	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16