

ÖLFLEX® FD 90

PVC PVC 가 -

ÖLFLEX® FD 90 - UL/CSA AWM

- 가 가

AWM



가 , 가

가

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® FD 90

IEC 60332-1-2 CSA FT1

VDE 0250 / 0285

UL-AWM-Style 10107, cRU AWM II A/B FT1 150mm²

CSA AWM IA/B IIA/B FT 1 120 mm²

UL File No. E63634

: 가 T3

(class 6)

: PVC

PVC , (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000057

ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057

ETIM 6.0 Class :

: - , 가

: VDE 0295 class 6, IEC 60228 class 6 가

: : 7.5 x

: 3 x

: IEC: U₀/U 600/1000 V

UL & CSA: 600 V

: 4000 V

: Flexing: -5°C to +70°C (UL: +90°C)

Fixed installation: -40°C to +80°C

(UL: +90°C)

: A2-1

, (:) 가
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® FD 90

	(mm ²)	(mm)		(kg/km)	(kg/km)
ÖLFLEX® FD 90					
0026600	10	9	-	96	176
0026601	10	9		96	176
0026603	16	10.5	-	153.6	240
0026604	16	10.5		153.6	240
0026607	25	11.8	-	240	361
0026608	25	11.8		240	361
0026610	35	14.2	-	336	482
0026611	35	14.2		336	482
0026613	50	16.2	-	480	660
0026614	50	16.2		480	660
0026616	70	18.3	-	672	898
0026617	70	18.3		672	898
0026619	95	19.8	-	912	1179
0026620	95	19.8		912	1179
0026622	120	23.4	-	1152	1521
0026623	120	23.4		1152	1521
0026625	150	25.1	-	1440	1739
0026626	150	25.1		1440	1739
0026628	185	28.1	-	1776	2305
0026629	185	28.1		1776	2305
0026634	240	31.6	-	2304	2944
0026635	240	31.6		2304	2944
0026640	300	33.5	-	2880	3545
0026641	300	33.5		2880	3545

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16