

# ÖLFLEX® SERVO 2XSLCH-JB

EMV

ÖLFLEX® SERVO 2XSLCH-JB -

, EMV

3+3

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



EMC-compliant operation of power drive systems

3+3

가

, 가  
,

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® SERVO 2XSLCH-JB

- (IEC 60332-1-2)
- (IEC 60754-1)
- (IEC 60754-2)
- (IEC 61034-2)
- (EN 50305)
- IEC 60332-3-24 IEC 60332-3-25 ( ) , -
- ISO 4892-2UV UV

VDE 0276, 0250, 0207

: XLPE (3+3 )  
 :  
 : (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC000057  
 ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000057  
 ETIM 6.0 Class :  
 : HD 308 S2 VDE 0293-308  
 : VDE 0295 5/ IEC 60228 5  
 가 가  
 : 15 x  
 : 4 x  
 : U0/U: 600/1000 V  
 : Core/Core: 4 kV  
 : Core/Screen: 4 kV  
 : G = GN-YE  
 : X =  
 : 3+3  
 : : -15°C ~ +90°C  
 : -40°C ~ +90°C

가 가 ( . ) 가 .  
 : [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m ).



# ÖLFLEX® SERVO 2XSLCH-JB

가 VAT 가 가 .

(24.04.2024)

# ÖLFLEX® SERVO 2XSLCH-JB

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SERVO 2XSLCH-JB / 4				
1133500	4 G 1.5	10.9	95	230
1133501	4 G 2.5	12.1	150	300
1133502	4 G 4.0	14.1	235	485
1133503	4 G 6.0	15.6	320	630
1133504	4 G 10.0	18	533	860
1133505	4 G 16.0	20.9	789	1290
1133506	4 G 25.0	26	1236	1860
1133507	4 G 35.0	29.6	1662	2610
1133508	4 G 50.0	32.8	2345	2950
1133509	4 G 70.0	38	3196	3950
1133510	4 G 95.0	42.5	4316	5300
1133511	4 G 120.0	47	5435	6600
1133512	4 G 150.0	52.9	6394	7590
1133513	4 G 185.0	57.6	7639	9420
ÖLFLEX® SERVO 2XSLCH-JB / 3+3				
1133514	3 X 1,5 + 3 G 0,25	10.9	88	177
1133515	3 X 2,5 + 3 G 0,5	12	144	230
1133516	3 X 4 + 3 G 0,75	13.5	224	323
1133517	3 X 6 + 3 G 1	14.7	276	420
1133518	3 X 10 + 3 G 1,5	16.7	491	635
1133519	3 X 16 + 3 G 2,5	20.2	723	930
1133520	3 X 25 + 3 G 4	23.4	1136	1350
1133521	3 X 35 + 3 G 6	26.7	1535	1780
1133522	3 X 50 + 3 G 10	30.9	2156	2530
1133523	3 X 70 + 3 G 10	34.4	2871	3225
1133524	3 X 95 + 3 G 16	38.3	3953	4511
1133525	3 X 120 + 3 G 16	42.3	4836	5663
1133526	3 X 150 + 3 G 25	47.5	5412	6720
1133527	3 X 185 + 3 G 35	51.9	7041	7855
1133528	3 X 240 + 3 G 50	59	8986	12850

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16