

# ÖLFLEX® SERVO 719



PVC

-

ÖLFLEX® SERVO 719 - UL/cUL AWM

ÖLFLEX® SERVO 700

Without overall screening



가  
, 가

가

:

(24.04.2024)

# ÖLFLEX® SERVO 719

UL/CSA: VW-1, FT1.  
IEC/EN: 60332-1-2

: UL AWM Style 2570  
: cUL AWM Style I/II A/B FT1  
UL File No. E63634

: (PP)  
:  
PVC , (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

: U/L1/C/L+ ; V/L2; W/L3/D/L-;  
GN/YE

: ,  
2 : ; 5; 6; 7; 8  
0,34mm<sup>2</sup> : / / /

: VDE 0295 5/ IEC 60228 5  
가 가

: : 15 x  
: 6 x

: :

U0/U: 600/1000 V  
UL & CSA: 1000 V

: Core/Core: 4 kV  
Core/Screen: 4 kV

: G = GN/YE

:  
-5°C ~ +70°C (UL: +80°C)  
: -40°C ~ +80°C

가 가 ( . ) 가  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

가 VAT 가 가 .

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1020060	4 G 1,5 + (2 x 0,75)	9.7	83.3	177
1020065	4 G 1,5 + (2 x 1,5)	10.8	108.3	214
1020061	5 G 1,5 + (2 x 0,75)	10.6	97.7	203
1020062	7 G 1,5 + (2 x 0,75)	11.5	126.5	241
1020063	4 G 2,5 + (2 x 0,75)	11.1	121.7	238
1020066	4 G 2,5 + (2 x 1,5)	12.2	146.7	276
1020064	7 G 2,5 + (2 x 0,75)	12.7	193.7	325
1020067	4 G 4 + (2 x 1,5)	13.9	204.3	360
1020068	4 G 6 + (2 x 1,5)	16.1	281.1	478
1020069	4 G 10 + (2 x 1,5)	18.2	434.7	654
1020071	4 G 0,75 + 2 x (2 x 0,34)	9.0	62.1	121
1020072	4 G 1,5 + 2 x (2 x 0,75)	11.6	111.6	203
1020073	4 G 2,5 + 2 x (2 x 1,0)	13.6	159.7	286
1020074	4 G 4 + 2 x (2 x 1,0)	15.3	217.3	377
1020075	4 G 4 + (2 x 1,0) + (2 x 1,5)	15.5	237.6	396
1020076	4 G 6 + (2 x 1,0) + (2 x 1,5)	17.4	314.4	512

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16