




ÖLFLEX® SERVO 728 CY

PVC

ÖLFLEX® SERVO 728 CY - UL/cUL AWM

ÖLFLEX® SERVO 720 CY



, 가

가

,

UV-

가

:

UL/CSA: VW-1, FT1.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO 728 CY

IEC/EN: 60332-1-2

UL AWM Style 2464
cUL AWM I/II A/B FT1
UL File No. E63634

: (PP)
()

PVC , (RAL 6018)

ETIM 5:	ETIM 5.0 Class-ID: EC000104
:	ETIM 5.0
:	ÖLFLEX® SERVO 728 CY
:	VDE 0295, Class 5 / IEC 60228 Class 5 가 (0.5mm ²)
:	: 15 x : 6 x
:	IEC: 30 V UL & CSA: 300 V
:	C/C: 2000 V C/S: 1000 V
:	: -5°C ~ +70°C (UL: +80°C) : -40°C ~ +80°C

가 가 () 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



ÖLFLEX® SERVO 728 CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1020100	(10x0,14+2x0,5)	7.0	41	84
1020101	(10x0,14+4x0,5)	7.6	53	101
1020102	(15x0,14+4x0,5)	7.6	68	115
1020133	(4x2x0,14+4x0,5)	7.9	58	97
1020134	(7x2x0,14+2x0,5)	8.5	60	115
1020110	(4x2x0,34+4x0,5)	8.3	79	129
1020111	(3x(2x0,14)+4x0,14+2x0,5)	8.2	68	120
1020135	(3x(2x0,14)+4x0,14+2x0,5+4x0,22)	9.7	80	160
1020120	(4x2x0,25+2x0,5)	7.9	59	103
1020121	(4x2x0,25+2x1,0)	7.6	63	112
1020122	(4x2x0,14+4x1,0+(4x0,14))	9.0	110	155
1020130	(3x(2x0,14)+2x(0,5))	9.0	87	140
1020136	3x(2x0,14)+(2x0,5)	9.3	87	140
1020131	3x(2x0,14)+(3x0,14)	9.2	41	115
1020132	4x(2x0,14)+(2x1,0)	10.4	84	145
1020140	(5x2x0,25)	7.4	50	96
1020141	(6x2x0,25)	8.0	60	114
1020142	(5x2x22AWG)	7.9	71	115

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16