

ÖLFLEX® CHAIN 896 P

PUR

ÖLFLEX® CHAIN 896 P - UL/CSA AWM

- 가

0,6/1kV



가 , 가

가 가

(22.07.2024)

ÖLFLEX® CHAIN 896 P

PUR

가 가

:
UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2

IEC 61892-4, D (MUD)
, -40°C

VDE - reg - no. 8661
UL AWM Style 20234
CSA AWM I/II, A 1000V 80° FT 1
UL File No. E63634

: 가 T3

: (class 6)
(PP)
, (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

: Black with white numbers acc. to VDE 0293-334
: VDE 0295 class 6, IEC 60228 class 6 가

: 7.5 x (16mm²)

10 x (25mm²)

: 4 x

: IEC U0/U: 600/1000 V
UL & CSA: 1000 V

(22.07.2024)



ÖLFLEX® CHAIN 896 P

: 4000 V
 : G = GN/YE
 : X = GN/YE
 : -40 ~ 90°C(UL/CSA: 80°C)
 : -50 ~ 90°C(UL/CSA: 80°C)
 : A2-1

, (:) 가
 www.lappkabel.de/en/cable-standradlengths

가 VAT 가 가 .

(22.07.2024)



ÖLFLEX® CHAIN 896 P

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CHAIN 896 P				
1023229	4 G 1.5	9.6	58	120
1023230	5 G 1.5	10	72	143
1023238	4 G 2.5	11	96	174
1023239	5 G 2.5	12	120	210
1023245	4 G 4.0	12.5	154	242
1023246	5 G 4.0	13.7	192	316
1023248	4 G 6.0	14.3	231	335
1023249	5 G 6.0	15.7	288	439
1023250	4 G 10.0	17	384	503
1023251	5 G 10.0	18.9	480	663
1023252	4 G 16.0	21.2	615	810
1023253	5 G 16.0	23.8	768	1065
1023254	4 G 25.0	25.9	960	1254
1023255	5 G 25.0	29	1200	1582

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16