

# ÖLFLEX® TRUCK 170 FLRYY

ÖLFLEX® TRUCK 170 FLRYY , , 60V DC, ADR, TÜV, ISO6722, ISO4141-3 PVC



ADR ADR

가

UV-

ISO 4141 DIN/ISO 6722

# ÖLFLEX® TRUCK 170 FLRYY

: PVC  
PVC-

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

:

ISO 4141-3

:

50 pF/m

, 100pF/m

:

DIN/ISO 6722

:

12 x

:

60 V

:

5 kV rms , 5 .

:

, Class A

: -40°C ~ +85°C

, 가 가 . ( . ) 가 .

[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

ÖLFLEX® TRUCK 170 FLRYY

Article number	(CORE) / (mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
ÖLFLEX® TRUCK 170 FLRYY					
7027060	2 x 1,0	6	-	19.2	55
7027061	2 x 1,0	6	-	19.2	55
7027000	2 x 1,5	6.6	-	28.8	68
7027001	2 x 1,5	6.6	-	28.8	68
7027062	3 x 1,0	6.3	- -	28.8	63
7027012	3 x 1,0	6.3	/ / , ISO	28.8	63
7027063	4 x 1,0	6.8	/ / /	38.4	81
7027034	4 x 1,5	7.5	/ / /	57.6	106
7027064	5 x 1,0	7.5	/ / / /	48	97
7027065	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 =	72	133
7027066	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 =	72	133
7027015	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 = , ISO	72	133
7027016	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 = , ISO	72	133
7027007	7 x 0,75	7.6	/ / / / / / /	50.4	101
7027067	7 x 1,5	8.9	/ / / / / / /	100.8	166
7027068	6 x 1,5 + 1 x 2,5	10.3	ISO 4141 1.5 = / / / / / ; 2.5 =	110.4	187
7027069	8 x 1,5 + 1 x 2,5	11.7	ISO 4141 + /	139.2	239
7027070	10 x 1,5 + 3 x 2,5 + 1x(2x1,5)	14.4	가 ; 1.5 = no. 1 - 3, 5 - 8, 10 - 12; 2.5 = no. 4, 9, 13; 1.5 = no. 14, 15	244.8	391
7027010	10 x 1,5 + 3 x 2,5 + 1x(2x1,5)	14.4	ISO 12098	244.8	391
7027071	10 x 1,5 + 3 x 2,5	14.4	가 ; 1.5 = no. 1 - 3, 5 - 8, 10 - 12; 2.5 = no. 4, 9, 13	216	367

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



ÖLFLEX® TRUCK 170 FLRY

Article number	(CORE) / (mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
7027017	5 x 1,5 + 2 x 2,5	10.3	1.5 = / / / / ; 2.5 = /	120	217
7027004	8 x 1,5 + 5 x 2,5	14.8	1.5 = / / / / / / / - ; 2.5 = / / / / - / -	235.2	360
7027073	9 x 1,5 + 4 x 2,5	14.8	가 ; 1.5 = no. 2, 4 - 8, 10 - 12; 2.5 = no. 1, 3, 9, 13	225.6	352
7027074	4 x 6 + 1 x 1,5	13.7	1.5 = ; 6.0 = / / /	244.8	352