


# ÖLFLEX® TRAIN 327 C TW-E 300V

EN 50306-4 5E MM S

ÖLFLEX® TRAIN 327 C TW-E 300V - EN 50306-4 5E MM S, / 300/500V , EN  
45545: HL1-HL3, NF F 16-101: C/F1

EN 50306-4 class E, MM S EN 45545-2  
: -50°C ~ +125°C



(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® TRAIN 327 C TW-E 300V



EMC

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

EMC-

,

가

가

EN / IEC 가 :- EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2  
가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -  
EN 60332-3-24 / EN 60332-3-25 / EN 50305 .  
NF - 가 NF X 70-100- NF X 10-702- NF X 10-702 Cat. C1 and C2  
:- EN 50306 - EN 50306 - EN 50306 - EN 50306  
EN 50306  
EN 50355 , A

EN 50306-4 Klasse E, Typ MM S  
EN 45545-2 HL1, HL2, HL3  
NF F 16-101 - : C / F1 ( / )

, 19 37 , SRC ( )  
: EN 50306 가  
: 가  
:  
: EN 50306 가 - S2  
: EN 50306 가 S2  
:

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

:

가

(23.12.2023)

# ÖLFLEX® TRAIN 327 C TW-E 300V

|   |                                |                   |      |
|---|--------------------------------|-------------------|------|
| ： | SRC ( ) EN 50306-1             | 19                | 37   |
| ： | 5 x                            | ：                 | 10 x |
| ： | U0: 600 V AC U0/U: EN 50306 Um | 300/500 V AC: 550 | V AC |
| ： | 3,5 kV AC; 8,4 kV DC           |                   |      |
| ： | ： GOST( ) 20.57.406-81         | -45°C             |      |
|   | ~ +125°C(20,000 h) -50°C       |                   |      |
|   | ： -35°C ~ +105°C               | ： +160°C (5 )     |      |

： ≤ 30 kg or ≤ 250 m, (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

# ÖLFLEX® TRAIN 327 C TW-E 300V

| Article number | (CORE) / (mm <sup>2</sup> ) | (mm) | (kg/km) | (kg/km) |
|----------------|-----------------------------|------|---------|---------|
| 15327000       | 2x (2X0,5)                  | 10.7 | 38.87   | 178.98  |
| 15327001       | 3x (2X0,5)                  | 11.4 | 58.3    | 211.95  |
| 15327002       | 4x (2X0,5)                  | 12.4 | 77.74   | 253.53  |
| 15327003       | 7x (2X0,5)                  | 14.7 | 136.38  | 374.84  |
| 15327004       | 2x (2X0,75)                 | 11.5 | 51.5    | 212.9   |
| 15327005       | 3x (2X0,75)                 | 12.2 | 77.25   | 249.55  |
| 15327006       | 4x (2X0,75)                 | 13.4 | 103     | 306.77  |
| 15327007       | 7x (2X0,75)                 | 15.9 | 180.64  | 446.95  |
| 15327008       | 2x (2X1)                    | 11.9 | 63      | 234.98  |
| 15327009       | 3x (2X1)                    | 12.6 | 94.5    | 281.92  |
| 15327010       | 4x (2X1)                    | 13.8 | 126     | 341.82  |
| 15327011       | 7x (2X1)                    | 16.5 | 220.93  | 499.43  |
| 15327012       | 2x (2X1,5)                  | 13.9 | 90      | 317.42  |
| 15327013       | 3x (2X1,5)                  | 14.8 | 136     | 383.34  |
| 15327014       | 4x (2X1,5)                  | 16.3 | 181     | 491.8   |
| 15327015       | 7x (2X1,5)                  | 19.5 | 320     | 697.3   |