

ÖLFLEX® SERVO FD 796 CP

PUR

ÖLFLEX® SERVO FD 796 CP - UL/CSA AWM VDE 가

- 가



가 가 가

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO FD 796 CP

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2

VDE - Reg. - No. 8591
UL AWM Style 20234
CSA AWM I/II, A 1000V 80° FT 1
UL File No. E63634

: 가 T3

: (class 6)
(PP)
:

PUR , (RAL 2003)

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

: U/L1/C/L+ ; V/L2; W/L3/D/L-;
GN/YE

: ;
0.34 mm² : / / / 5, 6; 7; 8

: 1; 2; 3

: VDE 0295 class 6, IEC 60228 class 6 가

:
7.5 x (16mm²)

10 x (25mm²)

(22.07.2024)



ÖLFLEX® SERVO FD 796 CP

: 4 x

:

U0/U: 600/1000 V
UL & CSA: 1000 V

:

Core/Core: 4 kV
Core/Screen: 2 kV

:

G = GN/YE

:

: -40 ~ 90°C(UL/CSA: 80°C)
: -50 ~ 90°C(UL/CSA: 80°C)

:

A2-1

www.lappkabel.de/en/cable-standradlengths

(:) 가

가 VAT 가 가 .

(22.07.2024)

ÖLFLEX® SERVO FD 796 CP

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SERVO FD 796 CP				
0027950	4 G 1,5	9.1	79	140
0027951	4 G 2,5	10.6	129	197
0027952	4 G 4	11.9	186	268
0027953	4 G 6	14.5	296	397
0027954	4 G 10	17.5	449	591
0027955	4 G 16	21.6	716	955
0027956	4 G 25	25.2	1073	1337
0027957	4 G 35	28.6	1480	1769
0027958	4 G 50	33.4	2115	2468
0027930	4 G 0,75 + (2 x 0,5)	11.0	85.5	155
0027925	4 G 1 + (2 x 0,5)	11.5	97.4	164
0027931	4 G 1 + (2 x 1,0)	11.7	106.7	174
0027926	4 G 1,5 + (2 x 0,5)	12.0	117.2	187
0027948	4 G 1,5 + (2 x 1,0)	12.2	129.9	202
0027932	4 G 1,5 + (3 x 1,0)	12.0	143.8	220
0027985	4 G 1,5 + (3 x 1,0) + (2 x 0,75)	12.9	178.6	262
0027959	4 G 1,5 + (2 x 1,5)	11.6	135	261
0027990	4 G 1,5 + (4 x 0,5)	12.2	-	217
0027927	4 G 2,5 + (2 x 0,5)	12.6	161.2	243
0027978	4 G 2,5 + (2 x 1,0)	13.5	169.2	253
0027933	4 G 2,5 + (3 x 1,0)	13.5	204.3	294
0027986	4 G 2,5 + (3 x 1,0) + (2 x 0,75)	14.7	-	340
0027960	4 G 2,5 + (2 x 1,5)	13.4	188	318
0027991	4 G 2,5 + (4 x 0,5)	13.5	192.2	278
0027981	4 G 4 + (2 x 1,0)	14.8	238.9	359
0027934	4 G 4 + (3 x 1,0)	14.7	250	361
0027987	4 G 4 + (3 x 1,5) + (2 x 0,75)	16.3	334.7	462
0027961	4 G 4 + (2 x 1,5)	14.8	235	385
0027992	4 G 4 + (4 x 0,5)	14.9	238.2	345
0027982	4 G 6 + (2 x 1,0)	16.8	339.5	469
0027962	4 G 6 + (2 x 1,5)	16.8	329	486
0027935	4 G 6 + (3 x 1,5)	16.5	381.4	505
0027988	4 G 6 + (3 x 1,5) + (2 x 0,75)	18.2	441.2	561

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0027993	4 G 6 + (4 x 0,5)	16.9	344.9	460
0027983	4 G 10 + (2 x 1,0)	18.8	530.1	689
0027963	4 G 10 + (2 x 1,5)	19.4	515	701
0027936	4 G 10 + (3 x 1,5)	19.7	568.9	722
0027989	4 G 10 + (3 x 1,5) + (2 x 0,75)	21.9	612.4	824
0027994	4 G 10 + (4 x 0,5)	18.9	528.5	687
0027984	4 G 16 + (2 x 1,0)	22.8	786.7	985
0027964	4 G 16 + (2 x 1,5)	23.1	757	1048
0027937	4 G 16 + (3 x 1,5)	23.3	824.6	1030
0027995	4 G 16 + (4 x 0,5)	22.9	786.3	1008
0027965	4 G 25 + (2 x 1,5)	26.6	1147	1532
0027966	4 G 35 + (2 x 1,5)	30.9	1538	2097
0027967	4 G 50 + (2 x 1,5)	34.0	2181	2721
0027968	4 G 1,0 + 2 x (2 x 0,75)	11.6	138.4	284
0027969	4 G 1,5 + 2 x (2 x 0,75)	12.2	159	313
0027970	4 G 2,5 + 2 x (2 x 1,0)	14.6	207	395
0027980	4 G 4 + 2 x (2 x 1,0)	16.1	274	466
0027971	4 G 4 + (2 x 1,0) + (2 x 1,5)	16.3	344	485
0027972	4 G 6 + (2 x 1,0) + (2 x 1,5)	18.1	436	588
0027973	4 G 10 + (2 x 1,0) + (2 x 1,5)	21.8	610	819
0027974	4 G 16 + 2 x (2 x 1,5)	25.5	801	1135
0027975	4 G 25 + 2 x (2 x 1,5)	28.8	1187	1559
0027976	4 G 35 + 2 x (2 x 1,5)	30.9	1588	2093
0027977	4 G 50 + 2 x (2 x 2,5)	36.3	2557	2920

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16