



# ÖLFLEX® TRAIN 331 600V

EN 50264-3-1 M

ÖLFLEX® TRAIN 331 600V - EN 50264-3-1 , M, / , 0.6/1kV, EN 45545: HL1-HL3, NF F  
16-101: C/F0, NFPA 130

EN 50264-3-1 M EN 45545-2  
: -50°C ~ 120°C

Also available in red, blue and further colours



**CE UK CA**



(24.04.2024)

# ÖLFLEX® TRAIN 331 600V

Good chemical resistance please see Appendix T1

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

가 가

EN / IEC 가 :- EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2  
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -  
 EN 60332-3-24 / EN 60332-3-25 / EN 50305  
 Fire behaviour according to NF (item-specific, refer to data sheet):  
 - Toxicity of gases acc. to NF X 70-100  
 - Low smoke density acc. to NF X 10-702  
 - No flame propagation acc. to NF C 32-070,  
 Cat. C1 and C2  
 :- EN 50264-3-1 . - EN 50264-3-1 . - EN 50264-3-1 . - EN  
 50264-3-1 . - EN 50264-3-1/ EN 50305 . - EN  
 EN 50355 , A

EN 50264-3-1 Typ M  
 EN 45545-2 HL1, HL2, HL3  
 NF F 16-101 - : C / F0 ( / )  
 NFPA 130

: 가 EI 109  
 Colour: Refer to item list

ETIM 5: ETIM 5.0 Class-ID: EC000993  
 ETIM 5.0 Class :  
 ETIM 6: ETIM 6.0 Class-ID: EC000993  
 ETIM 6.0 Class :  
 : IEC 60228, Class 5 /  
 : : 12 mm: 3 x OD > 12 mm: 4 x OD  
 : : 12 mm: 4 x OD > 12 mm 20 mm: 5 x OD > 20  
 mm: 6 x OD (OD = )  
 : U0/U AC 0.6/1 kV  
 U<sub>m</sub> AC 1.2 kV  
 V<sub>0</sub> DC 0.9 kV  
 : 3,5 kV AC; 8,4 kV DC  
 : : GOST( ) 20.57.406-81 -45°C  
 ~ +120°C(20,000 h) -50°C

(24.04.2024)



# ÖLFLEX® TRAIN 331 600V

: -35°C ~ +90°C      : + 200°C (5 )

가      가      .      ( . )      가 .  
:      30 kg or      250 m,  
가      VAT      가      가 .

ÖLFLEX® TRAIN 331 600V

Article number	(mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
ÖLFLEX® TRAIN 331 600V - BK					
15331065	0.5	2.1		4.8	9
15331066	0.75	2.3		7.2	12
15331000	1.0	2.5		9.6	15
15331001	1.5	3.0		14.4	22
15331002	2.5	3.4		24	33
15331003	4.0	4.1		38.4	49
15331004	6.0	4.6		57.6	70
15331005	10.0	5.6		96	112
15331006	16.0	6.6		153.6	174
15331007	25.0	8.3		240	273
15331008	35.0	9.5		336	374
15331009	50.0	11.7		480	531
15331010	70.0	13.6		672	739
15331011	95.0	15.6		912	988
15331012	120.0	17.4		1152	1243
15331013	150.0	19.8		1440	1558
15331014	185.0	21.7		1776	1927
15331015	240.0	25.4		2304	2487
15331016	300.0	26.8		2880	3085
ÖLFLEX® TRAIN 331 600V - GN/YE					
15331067	0.5	2.1	/	4.8	9
15331068	0.75	2.3	/	7.2	12
15331017	1.0	2.5	/	9.6	15
15331018	1.5	3.0	/	14.4	22
15331019	2.5	3.4	/	24	33
15331020	4.0	4.1	/	38.4	49
15331021	6.0	4.6	/	57.6	70
15331022	10.0	5.6	/	96	112
15331023	16.0	6.6	/	153.6	174
15331024	25.0	8.3	/	240	273
15331025	35.0	9.5	/	336	374
15331026	50.0	11.7	/	480	531

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16



ÖLFLEX® TRAIN 331 600V

Article number	(mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
15331027	70.0	13.6	/	672	739
15331028	95.0	15.6	/	912	988
ÖLFLEX® TRAIN 331 600V - BU					
15331074	0.5	2.1		4.8	9
15331075	0.75	2.3		7.2	12
15331050	1.0	2.5		9.6	15
15331052	1.5	3.0		14.4	22
15331048	2.5	3.4		24	33
15331054	4.0	4.1		38.4	49
15331076	6.0	4.6		57.6	70
15331077	10.0	5.6		96	112
15331078	16.0	6.6		153.6	174
ÖLFLEX® TRAIN 331 600V - RD					
15331069	0.5	2.1		4.8	9
15331070	0.75	2.3		7.2	12
15331049	1.0	2.5		9.6	15
15331051	1.5	3.0		14.4	22
15331047	2.5	3.4		24	33
15331053	4.0	4.1		38.4	49
15331071	6.0	4.6		57.6	70
15331072	10.0	5.6		96	112
15331073	16.0	6.6		153.6	174
15331055	70.0	13.6		672	739
ÖLFLEX® TRAIN 331 600V - BN					
15331079	0.5	2.1		4.8	9
15331080	0.75	2.3		7.2	12
15331081	1.0	2.5		9.6	15
15331082	1.5	3.0		14.4	22
15331083	2.5	3.4		24	33
15331084	4.0	4.1		38.4	49
15331085	6.0	4.6		57.6	70
15331086	10.0	5.6		96	112

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16

ÖLFLEX® TRAIN 331 600V

Article number	(mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
15331087	16.0	6.6		153.6	174
ÖLFLEX® TRAIN 331 600V - GY					
15331106	0.5	2.1		4.8	9
15331107	0.75	2.3		7.2	12
15331056	1.0	2.5		9.6	15
15331057	1.5	3.0		14.4	22
15331058	2.5	3.4		24	33
15331059	4.0	4.1		38.4	49
15331062	6.0	4.6		57.6	70
15331060	10.0	5.6		96	112
15331061	16.0	6.6		153.6	174
ÖLFLEX® TRAIN 331 600V - OG					
15331108	0.5	2.1		4.8	9
15331109	0.75	2.3		7.2	12
15331110	1.0	2.5		9.6	15
15331111	1.5	3.0		14.4	22
15331112	2.5	3.4		24	33
15331113	4.0	4.1		38.4	49
ÖLFLEX® TRAIN 331 600V - WH					
15331100	0.5	2.1		4.8	9
15331101	0.75	2.3		7.2	12
15331102	1.0	2.5		9.6	15
15331103	1.5	3.0		14.4	22
15331104	2.5	3.4		24	33
15331105	4.0	4.1		38.4	49
ÖLFLEX® TRAIN 331 600V - GN					
15331088	0.5	2.1		4.8	9
15331089	0.75	2.3		7.2	12
15331090	1.0	2.5		9.6	15
15331091	1.5	3.0		14.4	22
15331092	2.5	3.4		24	33
15331093	4.0	4.1		38.4	49

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® TRAIN 331 600V

Article number	(mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® TRAIN 331 600V - YE				
15331094	0.5	2.1	4.8	9
15331095	0.75	2.3	7.2	12
15331096	1.0	2.5	9.6	15
15331097	1.5	3.0	14.4	22
15331098	2.5	3.4	24	33
15331099	4.0	4.1	38.4	49
ÖLFLEX® TRAIN 331 600V - VT				
15331114	0.5	2.1	4.8	9
15331115	0.75	2.3	7.2	12
15331116	1.0	2.5	9.6	15
15331117	1.5	3.0	14.4	22
15331118	2.5	3.4	24	33
15331119	4.0	4.1	38.4	49

(24.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® TRAIN 331 600V



(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16