

ÖLFLEX® SERVO FD 7TCE

TC-ER(UL) c(UL)

ÖLFLEX® SERVO FD 7TCE - UL TC-ER

- 가 가
(NFPA 70/NEC)/

NFPA 79



TC-ER 가 Flexible Motor Supply Cable Listings - 가

(24.04.2024)

ÖLFLEX® SERVO FD 7TCE

NEC

UL OIL RES I & II
CSA FT4 UL
-40°C Cold Bend; -25°C Cold Impact; 90°C Wet or Dry
Sunlight resistant()
Direct burial()

UL 1277 UL TC-ER ()
UL 2277 Flexible Motor Supply Cable
Class 1 Division 2 per NEC Article 501
c(UL) CIC FT4 (18AWG - 14AWG);
cRU AWM I/II A/B FT4
: 가 T3

: EPR

: 가 (TPE),

ETIM 5:

ETIM 5.0 Class-ID: EC000057
ETIM 5.0

: U/L1/C/L+ ; V/L2; W/L3/D/L-;

GN/YE

1 : /
2 : / 5, 6, 7, 8

USA: UL TC-ER, Flexible Motor SupplyCanada: c(UL) CIC/TC
FT4, cRU AWM I/II A/B FT4

VDE 0295 class 6, IEC 60228 class 6 가

: 7.5 x

: 5 x

UL TC: 600V
UL Flexible Motor Supply: 1000V
c(UL) CIC/TC: 600V
cRU AWM: 1000V

(24.04.2024)



ÖLFLEX® SERVO FD 7TCE

IEC U0/U: 600/1000 V

Core/Core: 4 kV

Core/Screen: 2 kV

G = GN/YE

: -5°C ~ +90°C

: -40°C ~ +90°C

A2-1

www.lappkabel.de/en/cable-standradlengths (:) 가

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
700750	4 G 1.5	10.2	90.782	174
700751	4 G 2.5	11.4	141.382	230
700752	4 G 4.0	13.1	200.911	319
700753	4 G 6.0	15.0	282.763	431
700754	4 G 1,5 + (2 x 1,5)	12.7	144.358	259
700755	4 G 2,5 + (2 x 1,5)	13.8	199.423	356
700756	4 G 4 + (2 x 1,5)	16.1	273.834	447
700757	4 G 6 + (2 x 1,5)	17.1	345.269	537
700758	4 G 1 + 2 x (2 x 1,0)	13.3	151.799	280
700759	4 G 1,5 + 2 x (2 x 1,0)	14.8	190.493	355
700760	4 G 2,5 + 2 x (2 x 1,0)	15.9	277.699	410
700761	4 G 4 + (2 x 1,0) + (2 x 1,5)	17.9	318.481	525
700762	4 G 6 + (2 x 1,0) + (2 x 1,5)	18.8	389.916	613

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16