

ÖLFLEX® CHAIN 809 SC

PVC PVC 가 -

ÖLFLEX® CHAIN 809 SC - UL/cUL AWM

0,6/1kV 가
AWM



가 , 가

가

가

(24.04.2024)

ÖLFLEX® CHAIN 809 SC

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2
DIN EN 50290-2-22(TM54)

VDE 0250 / 0285
UL-AWM-Style 10107
cRU AWM II A/B FT1
UL File No. E63634

: 가 T3

: PVC
PVC , (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC000057
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000057
ETIM 6.0 Class :

: - , 가

: VDE 0295 5/ IEC 60228 5
가 가

WTG : TW-0 & TW-1, T0

: Flexing: up from 10 x outer diameter
: 4 x

: IEC: U₀/U 600/1000 V
UL & CSA: 600 V

: 4000 V

: : 0°C~+70°C(UL: +90°C)
Fixed installation: -40°C to +80°C
(UL: +90°C)

: A2-1

, (:) 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® CHAIN 809 SC

	(mm ²)	(mm)		(kg/km)	(kg/km)
ÖLFLEX® CHAIN 809 SC					
1062900	6	7.4	-	57.6	101
1062901	6	7.4		57.6	101
1062902	10	9	-	96	158
1062903	10	9		96	158
1062904	16	9.9	-	153.6	217
1062905	16	9.9		153.6	217
1062906	25	11.3	-	240	307
1062907	25	11.3		240	307
1062908	35	13.1	-	336	427
1062909	35	13.1		336	427
1062910	50	15.9	-	480	611
1062911	50	15.9		480	611
1062912	70	17.6	-	672	778
1062913	70	17.6		672	778
1062914	95	19.8	-	912	1015
1062915	95	19.8		912	1015
1062916	120	23	-	1152	1296
1062917	120	23		1152	1296
1062918	150	24.8	-	1440	1597
1062919	150	24.8		1440	1597
1062920	185	27.1	-	1776	1971
1062921	185	27.1		1776	1971
1062922	240	30.6	-	2304	2419
1062923	240	30.6		2304	2419

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16