


# ÖLFLEX® TRAIN 350 300V

EN 50264-3-2      MM

ÖLFLEX® TRAIN 350 300V -      EN 50264-3-2 MM, 300/500V,      /

EN 45545 : HL1-HL3, NF F 16-101: C/F0

EN 50264-3-2      MM      EN 45545-2  
: -50°C ~ 120°C



(05.05.2024)

# ÖLFLEX® TRAIN 350 300V



Good chemical resistance please see Appendix T1

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

, , , ,

EN / IEC 가 : - EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2  
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -  
 EN 60332-3-24 / EN 60332-3-25 / EN 50305 .  
 NF - 가 NF X 70-100- NF X 10-702- NF X 10-702 Cat. C1 and C2  
 : - EN 50264-3-2 - EN 50264-3-2 - EN 50264-3-2 - EN  
 50264-3-2 - EN 50264-3-2 / EN 50305  
 EN 50355 , A

EN 50264-3-2 Typ MM  
 EN 45545-2 HL1, HL2, HL3  
 NF F 16-101 - : C / F0 ( / )

: 가 EI 109  
 :  
 : 가 EM 104  
 :

ETIM 5: ETIM 5.0 Class-ID: EC000104  
 ETIM 5.0  
 ETIM 6: ETIM 6.0 Class-ID: EC000104  
 ETIM 6.0 Class :  
 : 가  
 : IEC 60228, Class 5 /  
 : : 12 mm: 3 x OD > 12 mm: 4 x OD  
 : : 12 mm: 4 x OD > 12 mm 20 mm: 5 x OD > 20  
 mm: 6 x OD (OD = )  
 : U0/U: 300/500 V  
 U<sub>m</sub> AC 600 V  
 V<sub>0</sub> DC 450 V  
 : 2,0 kV AC; 4,8 kV DC

(05.05.2024)



# ÖLFLEX® TRAIN 350 300V

: G = GN-YE  
 X =  
 : GOST( ) 20.57.406-81 -45°C  
 ~ +120°C(20,000 h) -50°C  
 : -35°C ~ +90°C : + 200°C (5 )

: 30 kg or 250 m, 가 가 ( . ) 가 .  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 가 VAT 가 가 .



# ÖLFLEX® TRAIN 350 300V

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
15350000	2 X 1.0	5.4	19.2	54.4
15350001	4 X 1.0	6.2	38.4	81.4
15350002	7 X 1.0	7.7	67.2	128.1
15350003	9 X 1.0	9.6	86.4	179.4
15350004	12 X 1.0	10.1	115.2	203.8
15350005	19 X 1.0	12.1	182.4	309
15350006	24 X 1.0	14.4	230.4	396.4
15350007	32 X 1.0	15.9	307.2	520.1
15350008	37 X 1.0	16.7	355.2	580.1
15350009	40 X 1.0	17.8	384	643.9
15350010	4 X 1.5	7.6	57.6	116.2
15350011	7 X 1.5	9.2	100.8	184
15350012	9 X 1.5	11.7	129.6	272.6
15350013	12 X 1.5	12.4	172.8	301.8
15350014	19 X 1.5	15.0	273.6	472.9
15350015	24 X 1.5	17.3	345.6	576.5
15350016	32 X 1.5	19.6	460.8	777.6
15350017	37 X 1.5	20.6	532.8	879.4
15350018	4 X 2.5	8.6	96	168.5
15350019	7 X 2.5	10.6	168	269.8
15350020	9 X 2.5	13.7	216	401.7
15350021	12 X 2.5	14.5	288	460.2
15350022	19 X 2.5	17.0	456	679.6
15350023	24 X 2.5	20.1	576	879.2

(05.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16