

ÖLFLEX® CHAIN 809

PVC

PVC

-

ÖLFLEX® CHAIN 809 - UL/cUL AWM

- 가
AWM



가 , 가

WTG()
:

(24.04.2024)



ÖLFLEX® CHAIN 809

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2

UL AWM Style 20886
cUL AWM II A/B FT1
UL File No. E63634

: 가 T3

: PVC

(RAL 7001) PVC

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

VDE 0295 5/ IEC 60228 5
가 가

WTG :

TW-0 & TW-1, T0

:

Flexing: up from 10 x outer diameter
: 4 x

:

VDE: U0/U: 300/500 V
UL & CSA: 1000 V

:

4000 V

:

G = GN/YE
X = GN/YE

:

: VDE 0 °C +70 °C (UL/CSA: +80°C)
: VDE -40 °C +70 °C; (UL/CSA +80°C)

:

A2-1

www.lappkabel.de/en/cable-standradlengths

: 100 m; (500; 1000) m

가 VAT

가

가

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CHAIN 809

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CHAIN 809				
1026700	2 X 0.5	5.2	10	40
1026701	3 G 0.5	5.5	15	48
1026702	4 G 0.5	6	20	58
1026703	5 G 0.5	6.5	24	67
1026704	7 G 0.5	7.7	34	88
1026705	12 G 0.5	9.2	58	136
1026706	18 G 0.5	11	87	195
1026707	25 G 0.5	13.3	120	274
1026708	2 X 0.75	5.6	15	49
1026709	3 G 0.75	6	22	60
1026710	4 G 0.75	6.5	29	73
1026711	5 G 0.75	7.1	37	86
1026712	7 G 0.75	8.5	51	117
1026713	12 G 0.75	10.3	87	181
1026714	18 G 0.75	12.2	130	259
1026715	25 G 0.75	14.8	181	363
1026716	2 X 1.0	5.9	19	58
1026717	3 G 1.0	6.3	29	72
1026718	4 G 1.0	6.9	39	88
1026719	5 G 1.0	7.5	48	104
1026720	7 G 1.0	9	67	142
1026721	12 G 1.0	10.9	115	221
1026722	18 G 1.0	13.2	173	324
1026723	25 G 1.0	15.7	240	445
1026724	2 X 1.5	6.5	29	74
1026725	3 G 1.5	6.9	43.2	93
1026726	4 G 1.5	7.6	58	114
1026727	5 G 1.5	8.5	72	139
1026728	7 G 1.5	10.3	101	189
1026729	12 G 1.5	12.3	173	295
1026730	18 G 1.5	14.9	259	429
1026731	25 G 1.5	17.9	360	597
1026732	3 G 2.5	8.4	72	145

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



ÖLFLEX® CHAIN 809

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1026733	4 G 2.5	9.3	96	179
1026734	7 G 2.5	12.7	168	218
1026737	4 G 4.0	11.1	160	266

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16