

ÖLFLEX® TRAIN 355 C 300V

EN 50264-3-2 MM S

ÖLFLEX® TRAIN 355 C 300V - EN 50264-3-2 MM S 300/500V, /

EN 45545: HL1-HL3, NF F 16-101: C / F0

EN 50264-3-2 MM S EN 45545-2
: -50°C ~ 120°C



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 355 C 300V



(,)

Good chemical resistance please see Appendix T1

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

, , , 가 가

EN / IEC 가 :- EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -
 EN 60332-3-24 / EN 60332-3-25 / EN 50305 .
 NF - 가 NF X 70-100- NF X 10-702- NF X 10-702 Cat. C1 and C2
 :- EN 50264-3-2 - EN 50264-3-2 - EN 50264-3-2 - EN
 50264-3-2 - EN 50264-3-2 / EN 50305 - EN
 EN 50355 , A

EN 50264-3-2 Typ MM S
 EN 45545-2 HL1, HL2, HL3
 NF F 16-101 - : C / F0 (/)

:
 : 가 EI 109
 :
 :
 : 가 EM 104
 :

ETIM 5: ETIM 5.0 Class-ID: EC000104
 ETIM 5.0
 ETIM 6: ETIM 6.0 Class-ID: EC000104
 ETIM 6.0 Class :
 : 가
 : IEC 60228, Class 5 /
 : 12 mm: 3 x OD > 12 mm: 4 x OD
 : 12 mm: 4 x OD > 12 mm 20 mm: 5 x OD > 20
 mm: 6 x OD (OD =)

(23.04.2024)

ÖLFLEX® TRAIN 355 C 300V

: U0/U: 300/500 V
 U_m AC 600 V
 V₀ DC 450 V
 : 2,0 kV AC; 4,8 kV DC
 : G = GN-YE
 X =
 : : GOST() 20.57.406-81 -45°C
 ~ +120°C(20,000 h) -50°C
 : -35°C ~ +90°C : + 200°C (5)

: 30 kg or 250 m, 가 가 (.) 가 .
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



ÖLFLEX® TRAIN 355 C 300V

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
15355000	2 X 1.0	6.2	39.27	71.4
15355001	4 X 1.0	7.2	64.06	108.5
15355002	7 X 1.0	8.5	97.15	152
15355003	9 X 1.0	10.8	137.41	234.1
15355004	12 X 1.0	11.3	170.09	257.7
15355005	19 X 1.0	13.7	261.77	395
15355006	24 X 1.0	15.6	324.51	482.2
15355007	32 X 1.0	17.1	411.92	605.9
15355008	37 X 1.0	17.9	471.56	685.9
15355009	40 X 1.0	19.4	510.27	777.3
15355010	4 X 1.5	8.4	86.8	145.1
15355011	7 X 1.5	10.2	150.51	224
15355012	9 X 1.5	13.1	191.37	336
15355013	12 X 1.5	13.8	240	371.1
15355014	19 X 1.5	16.2	369.09	547.8
15355015	24 X 1.5	18.9	463.04	697.9
15355016	32 X 1.5	20.8	591.57	891.5
15355017	37 X 1.5	21.8	664.73	993.6
15355018	4 X 2.5	9.6	153.75	219.6
15355019	7 X 2.5	11.6	224.75	311.4
15355020	9 X 2.5	14.9	309.28	478.1
15355021	12 X 2.5	15.7	382.12	529.9
15355022	19 X 2.5	18.6	573.02	794.6
15355023	24 X 2.5	21.3	718.82	999.1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16