

ÖLFLEX® FD 90 CY

PVC PVC -

ÖLFLEX® FD 90 CY - UL/CSA AWM

- 가 가
AWM
EMC



, 가

(,)

가

가

ÖLFLEX® FD 90 CY

IEC 60332-1-2 CSA FT1

EMC-

VDE 0250 / 0285

UL-AWM-Style 10107, cRU AWM II A/B FT1 $\geq 150\text{mm}^2$

CSA AWM IA/B IIA/B FT 1 $\leq 120\text{mm}^2$

UL File No. E63634

: 가 T3

(class 6)

: PVC

PVC , (RAL 2003)

ETIM 5:

ETIM 5.0 Class-ID: EC000057
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057
ETIM 6.0 Class :

: , 가

: VDE 0295 class 6, IEC 60228 class 6 가

: : 7.5 x

: 3 x

: IEC: U_0/U 600/1000 V

UL & CSA: 600 V

: 4000 V

: Flexing: -5°C to $+70^\circ\text{C}$ (UL: $+90^\circ\text{C}$)

Fixed installation: -40°C to $+80^\circ\text{C}$

(UL: $+90^\circ\text{C}$)

: A2-1

, (:) 가
www.lappkabel.de/en/cable-standradlengths

: $\leq 30\text{ kg}$ or $\leq 250\text{ m}$,

(e.g. 1 x 500 m or 5 x 100 m).

DESINA - Decentralized and standardized installation technology for machine tools and manufacturing systems

가 VAT 가 가 .

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® FD 90 CY

	(mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® FD 90 CY				
0026651	10	9.7	127.6	227
0026653	16	11.2	186.2	297
0026655	25	12.5	257.8	410
0026657	35	15.1	400.7	607
0026659	50	17.1	554.8	808
0026661	70	19.4	775.6	1081
0026663	95	20.9	1,028.1	1382
0026665	120	24.5	1,282.4	1752
0026667	150	26.2	1578	1924
0026669	185	29.2	1935	2611
0026671	240	32.9	2526	3372
0026673	300	34.8	3,128.8	4105