

# ÖLFLEX® TRAIN HT 150 F 3,6kV

EN 50382-2 F

ÖLFLEX® TRAIN HT 150 F 3.6kV - EN 50382-2 F , 3.6/6kV, 150°C, / , EN 45545: HL1-HL3

EN 50382-2 F EN 45545-2  
High temperature resistance: -40°C up to +150°C



(24.04.2024)

# ÖLFLEX® TRAIN HT 150 F 3,6kV

Good chemical resistance please see Appendix T1

For high ambient temperatures

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

가 가

EN / IEC 가 :- EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2  
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -  
 EN 60332-3-24 / EN 60332-3-25 / EN 50305  
 :- EN 50382-2 - EN 50382-2 - EN 50382-2 - EN 50382-2

EN 50355 , A

EN 50382-2 F  
 EN 45545-2 HL1, HL2, HL3

Insulation: Silicone rubber compound, type EI 111  
 :

ETIM 5:

ETIM 5.0 Class-ID: EC000057  
 ETIM 5.0

: VDE 0295 5/ IEC 60228 5  
 가 가  
 : 3 x  
 : 5 x

: U<sub>0</sub>/U AC 3,6/6 kV  
 U<sub>m</sub> AC 7,2 kV  
 V<sub>0</sub> DC 5,4 kV

: 11 kV AC; 26 kV DC

: -40°C ~ +150°C

: 30 kg or 250 m, 가 가 ( . ) 가 .  
 . (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® TRAIN HT 150 F 3,6KV

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
15382020	1 X 2.5	8.3	24	84
15382021	1 X 4.0	8.8	38.4	102
15382022	1 X 6.0	9.8	57.6	124
15382023	1 X 10.0	10.3	96	170
15382024	1 X 16.0	11.4	153.6	241
15382025	1 X 25.0	12.8	240	329
15382026	1 X 35.0	14.1	336	422
15382027	1 X 50.0	15.7	480	571
15382028	1 X 70.0	17.5	672	760
15382029	1 X 95.0	19.0	912	984
15382030	1 X 120.0	21.0	1152	1216
15382031	1 X 150.0	22.6	1440	1474
15382032	1 X 185.0	24.6	1776	1810

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16