


ÖLFLEX® TRAIN HT 150 FX 3,6kV

EN 50382-2 FX

ÖLFLEX® TRAIN HT 150 FX 3.6kV - EN 50382-2 FX , 3.6/6kV, 150°C, / , EN 45545: HL1-HL3

EN 50382-2 FX EN 45545-2
High temperature resistance: -40°C up to +150°C



(24.04.2024)

ÖLFLEX® TRAIN HT 150 FX 3,6kV

Good chemical resistance please see Appendix T1

For high ambient temperatures

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

EN / IEC 가 :- EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -
 EN 60332-3-24 / EN 60332-3-25 / EN 50305
 :- EN 50382-2 - EN 50382-2 - EN 50382-2 - EN 50382-2

EN 50355 , A

EN 50382-2 FX
 EN 45545-2 HL1, HL2, HL3

Insulation: Silicone rubber compound, type EI 111

ETIM 5:	ETIM 5.0 Class-ID: EC000057
:	ETIM 5.0
:	VDE 0295 class 6, IEC 60228 class 6 가
:	: 3 x
:	: 5 x
:	U ₀ /U AC 3,6/6 kV
:	U _m AC 7,2 kV
:	V ₀ DC 5,4 kV
:	11 kV AC; 26 kV DC
:	-40°C ~ +150°C

: 30 kg or 250 m, 가 가 (.) 가 .
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® TRAIN HT 150 FX 3,6kV

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
15382080	1 X 50.0	16.5	480	580
15382081	1 X 70.0	18.4	672	770
15382082	1 X 95.0	19.9	912	995
15382083	1 X 120.0	21.8	1152	1240
15382084	1 X 150.0	23.5	1440	1485
15382085	1 X 185.0	25.4	1776	1830

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16