


ÖLFLEX® SERVO 719 CY

PVC

ÖLFLEX® SERVO 719 CY - UL/cUL AWM

ÖLFLEX® SERVO 700 CY ÖLFLEX® SERVO 709 CY



가
, 가

가

(24.04.2024)

ÖLFLEX® SERVO 719 CY

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2

EMC-

: UL AWM Style 2570
: cUL AWM Style I/II A/B FT1
UL File No. E63634

: (PP)
:

(RAL 2003) PVC

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

: U/L1/C/L+ ; V/L2; W/L3/D/L-;
GN/YE

: ; 5; 6; 7; 8 ;

0.34 mm² : / / /

: 1; 2; 3

: VDE 0295 5/ IEC 60228 5
가 가

: 15 x
: 6 x

: :

U0/U: 600/1000 V
UL & CSA: 1000 V

: Core/Core: 4 kV
Core/Screen: 4 kV

: G = GN/YE

:
-5°C ~ +70°C (UL: +80°C)
: -40°C ~ +80°C

가 가 (.) 가
www.lappkabel.de/en/cable-standradlengths

(24.04.2024)



ÖLFLEX® SERVO 719 CY

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® SERVO 719 CY

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SERVO 719 CY				
1020010	4 G 1,5	8.4	83	130
1020011	4 G 2,5	9.9	125	190
1020012	4 G 4	11.7	191	273
1020013	4 G 6	13.7	290	394
1020014	4 G 10	16.7	452	581
1020015	4 G 16	20.1	721	884
1020016	4 G 25	24.3	1100	1348
1020017	4 G 35	27.7	1548	1840
1020018	4 G 50	33.7	2151	2645
1020040	4 G 0,75 + (2 x 0,5)	8.9	78	159
1020041	4 G 1 + (2 x 0,5)	9.3	88	147
1020044	4 G 1 + (2 x 1,0)	10.2	107	204
1020042	4 G 1,5 + (2 x 0,5)	10.3	111	180
1020045	4 G 1,5 + (2 x 1,0)	10.8	130	230
1020053	4 G 1,5 + (3 x 1,0)	11.5	145	225
1020019	4 G 1,5 + (2 x 1,5)	11.5	146	242
1020043	4 G 2,5 + (2 x 0,5)	11.7	158	247
1020046	4 G 2,5 + (2 x 1,0)	12.1	173	293
1020054	4 G 2,5 + (3 x 1,0)	12.9	188	290
1020020	4 G 2,5 + (2 x 1,5)	12.9	189	306
1020047	4 G 4 + (2 x 1,0)	14.3	250	373
1020055	4 G 4 + (3 x 1,0)	14.8	270	402
1020021	4 G 4 + (2 x 1,5)	15	271	420
1020048	4 G 6 + (2 x 1,0)	16.0	334	485
1020022	4 G 6 + (2 x 1,5)	17	351	529
1020056	4 G 6 + (3 x 1,5)	17.0	370	537
1020049	4 G 10 + (2 x 1,0)	18.8	526	712
1020023	4 G 10 + (2 x 1,5)	19.5	540	752
1020057	4 G 10 + (3 x 1,5)	19.5	559	758
1020050	4 G 16 + (2 x 1,0)	22.3	772	991
1020051	4 G 16 + (2 x 1,5)	22.5	785.2	999
1020058	4 G 16 + (3 x 1,5)	23.0	805	1151

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1020052	4 G 25 + (2 x 1,5)	26.1	1,184.9	1459
1020059	4 G 35 + (2 x 1,5)	30.4	1,598.1	1971
1020085	4 G 50 + (2 x 1,5)	34.0	2,205.2	2713
1020024	4 G 0,75 + 2 x (2 x 0,34)	9.7	99	163
1020035	4 G 1 + 2 x (2 x 0,75)	11.3	126.4	207
1020025	4 G 1,5 + 2 x (2 x 0,75)	12.3	150	245
1020026	4 G 2,5 + 2 x (2 x 1,0)	14.7	223	357
1020027	4 G 4 + 2 x (2 x 1,0)	16.4	288	452
1020028	4 G 4 + (2 x 1,0) + (2 x 1,5)	16.6	307	469
1020029	4 G 6 + (2 x 1,0) + (2 x 1,5)	18.5	421	617
1020030	4 G 10 + (2 x 1,0) + (2 x 1,5)	22.1	588	852
1020031	4 G 16 + 2 x (2 x 1,5)	25	876	1162
1020032	4 G 25 + 2 x (2 x 1,5)	28.7	1227	1590
1020033	4 G 35 + 2 x (2 x 1,5)	30.6	1652	2023
1020034	4 G 50 + 2 x (2 x 2,5)	37	2264	2876

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16