

ÖLFLEX® CLASSIC 110 H SF

, EN 45545-2 ,

ÖLFLEX® CLASSIC 110 H SF - , HFFR, , , -30°C
EN 45545-2

EN 45545-2 HL1, HL2, HL3

가



CE UK CA



(24.04.2024)



ÖLFLEX® CLASSIC 110 H SF

가
EN 45545-2

가

, IEC 60332-1-2
()
IEC 60332-3-24 IEC 60332-3-25 () , -
IEC 60754-1
(가)
IEC 60754-2 () , 가
IEC 61034-2
EN 50363-4-1(TM5)
UL OIL RES I UL OIL RES II
ISO 4892-2UV UV
EN 50396

EN 45545-2 HL1, HL2, HL3
EN 50525-3-11
EN 50525-2-51

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

VDE 0295 class 6, IEC 60228 class 6 가

:

: 10 x

: 4 x

:

U0/U: 300/500 V

:

4000 V

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CLASSIC 110 H SF

: G = GN/YE
 X = GN/YE
 : -30 °C ~ +70 °C
 : -40°C bis +80°C

, 가 가 . (.) 가 .
 : www.lappkabel.de/en/cable-standradlengths
 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

ÖLFLEX® CLASSIC 110 H SF

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1002140	5 G 0.5	6.3	24	83
1002141	3 G 1.0	6.1	28.8	75
1002142	5 G 1.0	7.3	48	123
1002143	7 G 1.0	8.1	67.2	159
1002144	13 G 1.0	11.4	124.8	295
1002145	25 G 1.0	15.0	240	515
1002146	43 G 1.0	19.8	412.8	899
1002147	73 G 1.0	25.3	700.8	1402
1002148	3 G 1.5	6.8	43.2	96
1002149	5 G 1.5	8.3	72	163
1002150	7 G 1.5	9.0	100.8	208
1002151	13 G 1.5	13.0	187.2	394
1002152	25 G 1.5	17.2	360	704
1002153	43 G 1.5	22.6	619.2	1198
1002154	61 G 1.5	25.6	878.4	1637
1002155	3 G 2.5	8.3	72	147
1002156	5 G 2.5	10.1	120	255
1002157	7 G 2.5	11.2	168	333
1002158	3 G 6.0	11.7	172.8	321
1002159	5 G 6.0	14.5	288	541
1002160	7 G 6.0	16.0	403.2	712
1002161	5 G 10.0	18.4	480	915
1002162	5 G 16.0	22.3	768	1344
1002163	5 G 35.0	31.1	1680	2778

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16