

ÖLFLEX® CLASSIC 110 H

ÖLFLEX® CLASSIC 110 H - , HFFR, , -30°C
CPR

CPR: www.lappkabel.com/cpr

A temporary outdoor use is possible



가

Note: for the use of AWM (Appliance Wiring Material) cables in industrial machinery (USA) according to NFPA 79: please see the catalogue appendix table T29

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 110 H

(CPR) T14
Considering the temperature range, a temporary outdoor use is possible

, IEC 60332-1-2
()
IEC 60332-3-22 IEC 60332-3-24 IEC 60332-3-25 ()
UL Cable Flame Test
IEC 60754-1
(가)
IEC 60754-2 () , 가
IEC 61034-2
EN 50363-4-1(TM5)
UL OIL RES I UL OIL RES II
ISO 4892-2UV UV
EN 50396

UL AWM 21089
EN 50525-3-11
EN 50525-2-51
DNV GL certificate no. TAE0000407

가
:
, (RAL 7001)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	IEC 60228/VDE 0295 class 5
:	: 10 x : 4 x
:	U0/U: 300/500 V UL: 600 V
:	4000 V
:	G = GN/YE X = GN/YE



ÖLFLEX® CLASSIC 110 H

: -30~70°C(UL: 75°C)
: -40~80°C(UL: 75°C)

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

ÖLFLEX® CLASSIC 110 H

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 110 H U0/U: 300/500 V				
10019900	2 X 0.5	5.1	9.6	41
10019901	3 G 0.5	5.4	14.4	49
10019902	3 X 0.5	5.4	14.4	49
10019903	4 G 0.5	5.8	19.2	58
10019904	4 X 0.5	5.8	19.2	58
10019905	5 G 0.5	6.3	24	69
10019906	7 G 0.5	6.9	33.6	87
10019907	12 G 0.5	9.1	57.6	141
10019910	2 X 0.75	5.5	14.4	51
10019911	3 G 0.75	5.8	21.6	61
10019912	3 X 0.75	5.8	21.6	61
10019913	4 G 0.75	6.3	28.8	73
10019914	4 X 0.75	6.3	28.8	73
10019915	5 G 0.75	6.9	36	87
10019916	5 X 0.75	6.9	36	87
10019917	7 G 0.75	7.5	50.4	111
10019918	7 X 0.75	7.5	50.4	111
10019919	9 G 0.75	9.6	64.8	150
10019920	12 G 0.75	10.1	86.4	186
10019921	18 G 0.75	12	129.6	265
10019922	25 G 0.75	14.1	180	365
10019960	2 X 1.0	5.8	19.2	59
10019961	3 G 1.0	6.1	28.8	72
10019962	3 X 1.0	6.1	28.8	72
10019963	4 G 1.0	6.6	38.4	87
10019964	4 X 1.0	6.6	38.4	87
10019965	5 G 1.0	7.3	48	104
10019967	7 G 1.0	8.1	67.2	138
10019968	8 G 1.0	9.7	76.8	164
10019969	12 G 1.0	10.7	115.2	225
10019970	14 G 1.0	11.4	134.4	261
10019971	18 G 1.0	12.9	172.8	328
10019972	25 G 1.0	15	240	445

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

ÖLFLEX® CLASSIC 110 H

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
10019973	41 G 1.0	19.2	393.6	719
10019930	2 X 1.5	6.4	28.8	76
10019931	3 G 1.5	6.8	43.2	94
10019980	3 X 1.5	6.8	43.2	94
10019932	4 G 1.5	7.4	57.6	115
10019933	5 G 1.5	8.3	72	142
10019934	7 G 1.5	9	100.8	184
10019981	8 G 1.5	10.8	115.2	218
10019982	9 G 1.5	11.6	129.6	245
10019935	12 G 1.5	12.2	172.8	308
10019936	14 G 1.5	13	201.6	357
10019937	18 G 1.5	14.6	259.2	449
10019938	25 G 1.5	17.2	360	617
10019927	34 G 1.5	19.8	489.6	821
10019944	2 X 2.5	7.6	48	113
10019945	3 G 2.5	8.3	72	146
10019946	4 G 2.5	9	96	180
10019947	5 G 2.5	10.1	120	221
10019948	7 G 2.5	11.2	168	295
10019949	12 G 2.5	15.1	288	491
10019950	4 G 4.0	10.8	153.6	268
10019951	5 G 4.0	12.1	192	328
10019952	7 G 4.0	13.4	268.8	438
10019953	4 G 6.0	13	230.4	391
10019954	5 G 6.0	14.5	288	478
10019975	7 G 6.0	16	403.2	638
10019851	4 G 10.0	16.2	384	635
10019852	5 G 10.0	18.1	480	775
10019849	4 G 16.0	18.8	614.4	930
10019853	5 G 16.0	21.2	768	1147
10019854	4 G 25.0	23.5	960	1442
10019855	5 G 25.0	26.4	1200	1773
10019856	4 G 35.0	26.6	1344	1917

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16