

ÖLFLEX® CLASSIC 115 CH SF

가
ÖLFLEX® CLASSIC 115 CH SF - , HFFR, , -30°C , EN
45545-2

EN 45545-2 HL1, HL2, HL3

가



(24.04.2024)

ÖLFLEX® CLASSIC 115 CH SF



가
EN 45545-2
EMC

EMC- , 가

, IEC 60332-1-2
()
IEC 60332-3-24 IEC 60332-3-25 () , -
IEC 60754-1
(가)
IEC 60754-2 () , 가
IEC 61034-2
EN 50363-4-1(TM5)
UL OIL RES I UL OIL RES II
ISO 4892-2UV UV
EN 50396

EN 45545-2 HL1, HL2, HL3
EN 50525-3-11
EN 50525-2-51

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

Black with white numbers acc. to VDE 0293-334

(24.04.2024)

ÖLFLEX® CLASSIC 115 CH SF

:	VDE 0295 class 6, IEC 60228 class 6	가
:	: 15 x : 6 x	
:	U0/U: 300/500 V	
:	Core/core: 4000 V Core/screen: 2000 V	
:	G = GN/YE X = GN/YE	
:	: -30 °C ~ +70 °C : -40°C bis +80°C	

가 가 () 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
: 4G50 500 m

가 VAT 가 가 .



ÖLFLEX® CLASSIC 115 CH SF

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1002164	5 G 0.5	7.1	43.3	97
1002165	36 X 0.5	16.1	267.1	538
1002166	3 G 0.75	6.6	40.9	86
1002167	5 G 0.75	7.9	58.1	122
1002168	7 G 0.75	8.5	85.8	160
1002169	25 G 0.75	15.1	248.4	485
1002170	7 G 1.0	8.9	92.3	172
1002171	13 G 1.0	12.4	162	318
1002172	25 G 1.0	16.2	306	600
1002173	2 X 1.5	7.2	56.5	103
1002174	3 G 1.5	7.6	65.3	119
1002175	5 G 1.5	9.1	108.9	186
1002176	4 G 2.5	10.0	124.9	217
1002177	4 G 4.0	11.9	188.2	303
1002178	4 G 6.0	14.2	271.7	443
1002179	4 G 10.0	17.5	453.8	725

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16