



ÖLFLEX® CLASSIC 130 H BK 0,6/1 kV

0.6/1kVAC, IEC 60332-3, IEC 61034-2, UV/ , UL AWM 1000V

ÖLFLEX® CLASSIC 130 H BK 0,6/1 kV UL AWM Style 21156, class 5, / ,

CPR: www.lappkabel.com/cpr

UL AWM

Easy handling and installation due to flexible design

가

According to NFPA 79, subchapter 12.9.2: Use for industrial machinery operated in the USA on the basis of UL AWM (recognized) certification

/ 가 1.8mm : 가

, IEC 60332-1-2

()

IEC 60332-3-24 IEC 60332-3-25 () , -

IEC 60754-1

(가)

IEC 60754-2 () , 가

IEC 61034-2

ISO 4892-2UV UV

EN 50396

EN 50525-3-11

UL AWM approval: refer to data sheet

가

:

ETIM 5:

ETIM 5.0 Class-ID: EC000057
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057
ETIM 6.0 Class :

(21.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CLASSIC 130 H BK 0,6/1 kV

:	5	: VDE 0293-308	.	T9
:	6	:		
:		IEC 60228/VDE 0295 class 5		
:		: 15 x		
:		: 4 x		
:		U0/U: 600/1000 V		
:		UL: 1,000V		
:		4000 V		
:		G = GN/YE		
:		X = GN/YE		
:		UL: +75°C	: -25°C ~ +70°C	: -40°C ~ +80°C

가 가 () 가
 www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

ÖLFLEX® CLASSIC 130 H BK 0,6/1 kV

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1123410	2 X 1.0	8.6	19.2	107
1123411	3 G 1.0	9	28.8	123
1123412	4 G 1.0	9.6	38.4	144
1123413	5 G 1.0	10.4	48	167
1123414	7 G 1.0	11.1	67.2	206
1123415	12 G 1.0	14	115.2	314
1123418	2 X 1.5	9.6	28.8	137
1123419	3 G 1.5	10.1	43.2	161
1123420	4 G 1.5	10.8	57.6	190
1123421	5 G 1.5	11.7	72	221
1123422	7 G 1.5	12.6	100.8	276
1123423	12 G 1.5	16.1	172.8	427
1123424	18 G 1.5	18.8	259.2	596
1123425	25 G 1.5	21.7	360	799
1123427	3 G 2.5	11.3	72	219
1123428	4 G 2.5	12.2	96	262
1123429	5 G 2.5	13.3	120	307
1123430	7 G 2.5	14.4	168	390
1123431	12 G 2.5	18.7	288	624
1123432	18 G 2.5	22	432	879
1123433	25 G 2.5	25.8	600	1212
1123434	3 G 4.0	12.6	115.2	290
1123435	4 G 4.0	13.7	153.6	351
1123436	5 G 4.0	14.9	192	416
1123437	3 G 6.0	13.9	172.8	377
1123438	4 G 6.0	15.1	230.4	463
1123439	5 G 6.0	16.8	288	559
1123440	4 G 10.0	18.7	384	662
1123441	5 G 10.0	20.7	480	915
1123442	4 G 16.0	21.3	614.4	1070
1123443	5 G 16.0	23.6	768	1296
1123444	4 G 25.0	26.2	960	1631

(21.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16