

ÖLFLEX® EB CY

IEC 60079-14/EN 60079-14/VDE 0165-1

ÖLFLEX® EB CY - 가 PVC , U
o/U: 300/500V

CPR: www.lappkabel.com/cpr
ISO 4892-2UV UV



ÖLFLEX® EB CY

IEC 60079-14:2013/EN 60079-14:2014/VDE 0165-1:2014, 16.2.2 (i -)
EMC-
()

: IEC 60332-1-2

(. 250 /km, 30 MHz)

(24.04.2024)

ÖLFLEX® EB CY

ISO 4892-2UV UV

EN 50525-2-51

PVC LAPP P8/1 가

RAL 5015 PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	Core/core approx. 160nF/kmCore/screen approx. 250nF/km
:	approx. 0.52 mH/km
:	IEC 60228/VDE 0295 class 5
:	: 20 x
:	: 6 x
:	U0/U: 300/500 V
:	Core/core: 3000 V Core/screen: 2000 V
:	: -5°C ~ +70°C : -40°C +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® EB CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® EB CY ;				
0012640	2 X 0.75	6.2	43	56
0012641	3 X 0.75	6.5	52	70
0012642	4 X 0.75	7	61	95
0012643	5 X 0.75	7.7	72	108
0012644	7 X 0.75	8.3	89	168
0012645	12 X 0.75	10.9	138	216
0012646	18 X 0.75	12.7	211	315
0012647	25 X 0.75	14.8	280	435
0012650	2 X 1.0	6.5	51	84
0012651	3 X 1.0	6.8	62	110
0012652	5 X 1.0	8.1	88	156
0012653	7 X 1.0	8.8	112	192
0012654	12 X 1.0	11.5	185	285
0012655	18 X 1.0	13.9	268	395
0012656	25 X 1.0	15.9	354	656
0012660	2 X 1.5	7.1	65	87
0012661	3 X 1.5	7.5	82	112
0012662	5 X 1.5	8.9	119	148
0012663	7 X 1.5	9.9	154	193
0012664	12 X 1.5	13	268	365
0012666	25 X 1.5	17.9	530	734

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16