

ÖLFLEX® TRAIN 320 TW-E 300V

EN 50306-4 1E MM

ÖLFLEX® TRAIN 320 TW-E 300V - EN 50306-4 1E MM , / 300/500V, EN 45545:
HL1-HL3, NF F 16-101: C/F0

EN 50306-4 class E, MM EN 45545-2
: -50°C ~ +125°C

LAPP KABEL STUTTGART ÖLFLEX® TRAIN 320 TW-E 300V EN 50306-4 1E MM



(25.04.2024)

ÖLFLEX® TRAIN 320 TW-E 300V



Good chemical resistance please see Appendix T1

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

가 가

EN / IEC 가 : - EN 60754-1 . - EN 60754-2 가 가 . - EN 60684-2
 가 . - EN 50305 가 가 . - EN 61034-2 . - EN 60332-1-2 . -
 EN 60332-3-24 / EN 60332-3-25 / EN 50305 .
 NF - 가 NF X 70-100- NF X 10-702- NF X 10-702 Cat. C1 and C2
 : - EN 50306 - EN 50306 - EN 50306 - EN 50306 -
 EN 50306
 EN 50355 , A

EN 50306-4 class E, type MM
 EN 45545-2 HL1, HL2, HL3
 NF F 16-101 - : C / F0 (/)

, 19 37 가 , SRC ()
 : EN 50306 가
 : 가
 : EN 50306 가 S2
 :

ETIM 5: ETIM 5.0 Class-ID: EC000104
 ETIM 5.0
 ETIM 6: ETIM 6.0 Class-ID: EC000104
 ETIM 6.0 Class :
 : 가
 : SRC () EN 50306-1 19 37
 : Ø 12 mm: 4 x OD / 3 x OD > 12 mm:
 5 x OD / 4 x OD
 : 12 mm: 5 x OD > 12 mm: 6 x OD (OD =)
 : U0: 600 V AC U0/U: EN 50306 Um 300/500 V AC: 550

(25.04.2024)

ÖLFLEX® TRAIN 320 TW-E 300V

		V AC	
:		3,5 kV AC; 8,4 kV DC	
:		G = GN-YE	
:		X =	
:		: GOST() 20.57.406-81	-45°C
		~ +125°C(20,000 h) -50°C	
		: -35°C ~ +105°C	: +160°C (5)
:	30 kg or 250 m,	가 가 (.) 가 .	
		(e.g. 1 x 500 m or 5 x 100 m) .	
가	VAT	가	가 .

(25.04.2024)



ÖLFLEX® TRAIN 320 TW-E 300V

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
15320000	4 X 0.5	6.0	19.2	60.95
15320001	7 X 0.5	6.8	33.6	84.17
15320002	13 X 0.5	8.8	62.4	142.1
15320003	19 X 0.5	9.6	91.2	180.85
15320004	37 X 0.5	12.9	177.6	332.58
15320005	4 X 0.75	6.5	28.8	76.4
15320006	7 X 0.75	7.4	50.4	108.28
15320007	13 X 0.75	9.7	93.6	185.94
15320008	19 X 0.75	10.6	136.8	240.31
15320009	37 X 0.75	13.8	266.4	427
15320011	4 X 1.0	6.8	38.4	90.13
15320012	7 X 1.0	7.8	67.2	130.21
15320013	13 X 1.0	10.3	124.8	226.12
15320014	19 X 1.0	11.3	182.4	295.72
15320015	37 X 1.0	14.8	355.2	531.56
15320016	4 X 1.5	7.9	57.6	124.75
15320017	7 X 1.5	9.3	100.8	189.27
15320018	13 X 1.5	12.3	187.2	325.41
15320019	19 X 1.5	13.6	273.6	433.31
15320020	37 X 1.5	18.0	532.8	782.39
15320021	2 X 2.5	8.2	49.2	126.39
15320022	3 X 2.5	8.6	73.79	151.93
15320023	4 X 2.5	9.4	98.39	188.61

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16