

# ÖLFLEX® TRAIN 325 C TW-E 300V

EN 50306-4 3E      MM S

ÖLFLEX® TRAIN 325 C TW-E 300V - EN 50306-4 3E      MM S,      /      300/500V      , EN  
45545: HL1-HL3, NF F 16-101: C/F0

EN 50306-4 class E, MM S      EN 45545-2  
: -50°C ~ +125°C



**CE UK  
CA**



(24.04.2024)

# ÖLFLEX® TRAIN 325 C TW-E 300V



EMC

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

EMC-

가

가

|  |   |                |              |              |             |              |            |                |
|--|---|----------------|--------------|--------------|-------------|--------------|------------|----------------|
| EN / IEC                                 | 가 | : - EN 60754-1 | .            | - EN 60754-2 | 가           | 가            | .          | - EN 60684-2   |
| 가  | . | - EN 50305     | 가            | 가            | .           | - EN 61034-2 | .          | - EN 60332-1-2 |
| EN 60332-3-24 / EN 60332-3-25 / EN 50305 | . | .              | .            | .            | .           | .            | .          | .              |
| NF                                       | . | - 가            | NF X 70-100- | NF X 10-702- | NF X 10-702 | .            | .          | Cat. C1 and C2 |
|  | : | - EN 50306     | - EN 50306   | - EN 50306   | - EN 50306  | .            | - EN 50306 | -              |
| EN 50306                                 | . | .              | .            | .            | .           | .            | .          | .              |
| EN 50355                                 | , | A              | .            | .            | .           | .            | .          | .              |

EN 50306-4 Klasse E, Typ MM S  
 EN 45545-2 HL1, HL2, HL3  
 NF F 16-101 - : C / F0 ( / )

:  
 , 19 37 , SRC ( )  
 : EN 50306 가  
 : 가  
 : ( )  
 :  
 : EN 50306 가 S2

ETIM 5: ETIM 5.0 Class-ID: EC000104  
 ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000104  
 ETIM 6.0 Class :  
 : 가

(24.04.2024)

# ÖLFLEX® TRAIN 325 C TW-E 300V

|   |                                |               |             |
|---|--------------------------------|---------------|-------------|
| : | SRC ( ) EN 50306-1             | 19            | 37          |
| : | 5 x                            | :             | 10 x        |
| : | U0: 600 V AC U0/U: EN 50306 Um | 300/500 V AC: | 550 V AC    |
| : | 3,5 kV AC; 8,4 kV DC           |               |             |
| : | G = GN-YE                      |               |             |
| : | X =                            |               |             |
| : | : GOST( ) 20.57.406-81         | -45°C         |             |
|   | ~ +125°C(20,000 h) -50°C       |               |             |
|   | : -35°C ~ +105°C               | :             | +160°C (5 ) |

가 가 ( . ) 가 .  
 : 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m ).  
 가 VAT 가 가 .



ÖLFLEX® TRAIN 325 C TW-E 300V

| Article number | (CORE) / (mm <sup>2</sup> ) | (mm) | (kg/km) | (kg/km) |
|----------------|-----------------------------|------|---------|---------|
| 15325000       | 2 X 0.5                     | 6.0  | 19.37   | 57.36   |
| 15325001       | 3 X 0.5                     | 6.2  | 24.88   | 64.85   |
| 15325002       | 4 X 0.5                     | 6.6  | 30.87   | 74.62   |
| 15325003       | 6 X 0.5                     | 7.4  | 42.95   | 95.06   |
| 15325004       | 8 X 0.5                     | 8.0  | 61.26   | 121.54  |
| 15325005       | 2 X 0.75                    | 6.4  | 25.67   | 65.89   |
| 15325006       | 3 X 0.75                    | 6.7  | 33.71   | 78.02   |
| 15325007       | 4 X 0.75                    | 7.0  | 42.18   | 89.21   |
| 15325008       | 6 X 0.75                    | 8.0  | 65.36   | 120.98  |
| 15325009       | 8 X 0.75                    | 8.7  | 83.99   | 153.1   |
| 15325010       | 2 X 1.0                     | 6.7  | 31.42   | 76.14   |
| 15325011       | 3 X 1.0                     | 7.0  | 41.97   | 89.46   |
| 15325012       | 4 X 1.0                     | 7.4  | 52.9    | 105.59  |
| 15325013       | 6 X 1.0                     | 8.5  | 81.75   | 144.07  |
| 15325014       | 8 X 1.0                     | 9.2  | 105.4   | 180.36  |
| 15325015       | 2 X 1.5                     | 7.6  | 44.09   | 98.95   |
| 15325016       | 3 X 1.5                     | 7.9  | 65.53   | 121.02  |
| 15325017       | 4 X 1.5                     | 8.5  | 82.14   | 145.09  |
| 15325018       | 6 X 1.5                     | 9.8  | 117.22  | 196.01  |
| 15325019       | 8 X 1.5                     | 10.8 | 151.94  | 249.75  |
| 15325020       | 2 X 2.5                     | 8.8  | 75.42   | 141.64  |
| 15325021       | 3 X 2.5                     | 9.2  | 102.07  | 173.32  |
| 15325022       | 4 X 2.5                     | 10.0 | 129.75  | 210.67  |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16