

ÖLFLEX® CLASSIC 110 CY

가 PVC

ÖLFLEX® CLASSIC 110 CY - PVC , VDE , , , U
o/U: 300/500V

CPR: www.lappkabel.com/cpr
VDE 7030
EMC-



4kV

EMC-
()

: IEC 60332-1-2

, T1

ÖLFLEX® CLASSIC 110 CY

(. 250 Ω /km, 30 MHz)

VDE 7030

가
PVC LAPP P8/1

PVC ,
PVC

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

•

•

Black with white numbers acc. to VDE 0293-334

$$\vdots$$

IEC 60228/VDE 0295 class 5

$$\begin{aligned} & \cdot \\ & \cdot \end{aligned}$$

: 20 x

: 6 x

$$\vdots$$

U0/U: 300/500 V

•

4000 V

$$\vdots$$
$$G = GN/YE$$
$$X = GN/YE$$
$$\vdots$$

: -5°C ~ +70°C

: -40°C +80°C

가 가 . (.) 가 .

www.lappkabel.de/en/cable-standradlengths

: ≤ 30 kg or ≤ 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02 03.16

ÖLFLEX® CLASSIC 110 CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 110 CY				
1135752	2 X 0.5	7	41	75
1135003	3 G 0.5	7.3	45.5	83
1135753	3 X 0.5	7.3	45.5	83
1135004	4 G 0.5	7.9	55	99
1135754	4 X 0.5	7.9	55	99
1135005	5 G 0.5	8.4	66	112
1135755	5 X 0.5	8.4	66	112
1135007	7 G 0.5	8.9	80.5	132
1135757	7 X 0.5	8.9	80.5	132
1135012	12 G 0.5	11.3	138.5	202
1135762	12 X 0.5	11.3	138.5	202
1135018	18 G 0.5	13.3	156.4	289
1135025	25 G 0.5	15.2	250	378
1135030	30 G 0.5	16.1	297	429
1135040	40 G 0.5	18.2	343	542
1135802	2 X 0.75	7.4	46	86
1135103	3 G 0.75	7.9	57.9	100
1135803	3 X 0.75	7.9	57.9	100
1135104	4 G 0.75	8.4	64	115
1135804	4 X 0.75	8.4	64	115
1135105	5 G 0.75	8.9	77.4	130
1135805	5 X 0.75	8.9	77.4	130
1135107	7 G 0.75	9.7	102	161
1135807	7 X 0.75	9.7	102	161
1135112	12 G 0.75	12.3	177	247
1135812	12 X 0.75	12.3	177	247
1135118	18 G 0.75	14.5	243	356
1135818	18 X 0.75	14.5	243	356
1135125	25 G 0.75	16.6	307.3	465
1135134	34 G 0.75	18.9	323.2	601
1135840	40 X 0.75	20.5	369.4	734
1135141	41 G 0.75	20.6	488	728
1135852	2 X 1.0	7.9	56	98

ÖLFLEX® CLASSIC 110 CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1135203	3 G 1.0	8.2	65.3	111
1135853	3 X 1.0	8.2	65.3	111
1135204	4 G 1.0	8.7	78.1	130
1135854	4 X 1.0	8.7	78.1	130
1135205	5 G 1.0	9.5	89.4	153
1135207	7 G 1.0	10.2	113.3	185
1135212	12 G 1.0	13.3	188.1	307
1135216	16 G 1.0	14.6	216	390
1135218	18 G 1.0	15.5	286	418
1135225	25 G 1.0	17.5	388.5	544
1135234	34 G 1.0	20.3	505	738
1135241	41 G 1.0	22	578	864
1135250	50 G 1.0	23.8	688	1011
1135902	2 X 1.5	8.5	65	117
1135303	3 G 1.5	8.9	83	136
1135903	3 X 1.5	8.9	83	136
1135304	4 G 1.5	9.6	100	163
1135904	4 X 1.5	9.6	100	163
1135305	5 G 1.5	10.3	125	188
1135905	5 X 1.5	10.3	125	188
1135307	7 G 1.5	11.3	149	237
1135907	7 X 1.5	11.3	149	237
1135312	12 G 1.5	14.8	280	393
1135318	18 G 1.5	17.2	389	538
1135325	25 G 1.5	20.1	535	745
1135334	34 G 1.5	22.8	702	964
1135341	41 G 1.5	24.7	844.6	1123
1135350	50 G 1.5	27.1	1006	1372
1135402	2 X 2.5	9.9	112	165
1135403	3 G 2.5	10.3	146	192
1135404	4 G 2.5	11.3	167	233
1135405	5 G 2.5	12.6	200	283
1135407	7 G 2.5	13.9	288	371
1135412	12 G 2.5	17.6	477.3	585

ÖLFLEX® CLASSIC 110 CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1135502	2 X 4.0	11.4	120	247
1135504	4 G 4.0	13.4	237	347
1135505	5 G 4.0	14.7	280	413
1135602	2 X 6.0	13.6	180	353
1135604	4 G 6.0	15.8	318	485
1135605	5 G 6.0	17.3	441	702
1135607	7 G 6.0	18.8	530	950
1135702	2 X 10.0	16.4	256	492
1135615	3 G 10.0	17.4	362.4	507
1135614	4 G 10.0	19	518	735
1135616	5 G 10.0	21.3	595	847
1135617	7 G 10.0	23.2	796	1039
1135622	2 X 16.0	18.6	390	698
1135624	4 G 16.0	22.2	804	1395
1135623	5 G 16.0	24.4	935	1440
1135626	4 G 25.0	26.9	1161	1730
1135627	5 G 25.0	30	1400	2090
1135625	4 G 35.0	30.2	1543	2210
1135628	5 G 35.0	33.2	1901	2710