


# ÖLFLEX® SMART 108

VDE PVC

ÖLFLEX® SMART 108 - VDE PVC , , , 300/500V, YSLY YY

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

VDE  
가



SMART: 가 – ÖLFLEX® SMART 108 가

SMART: – TM2 PVC

, 가 ÖLFLEX® CLASSIC 110  
ÖLFLEX® CLASSIC 110

: IEC 60332-1-2

T1

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® SMART 108

VDE . 8639

가

PVC , T12  
2 PVC , TM2,

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

DIN EN 60228(VDE 0295), class 5 / IEC 60228 class 5  
가

:

: 15 x

: 4 x

:

U0/U: 300/500 V

:

4000 V

:

G = GN/YE

X = GN/YE

:

: -5°C ~ +70°C

: -40°C +80°C

가 : EUR 100 , 150 kg.  
: = RG, = DR

가

가

( . )  
T17

가

가 VAT 가 가 .

(25.04.2024)

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
17520099	2 X 0.5	4.8	9.6	35
10030099	3 G 0.5	5.1	14.4	42
17530099	3 X 0.5	5.1	14.4	42
10040099	4 G 0.5	5.7	19.2	54
17540099	4 X 0.5	5.7	19.2	54
10050099	5 G 0.5	6.2	24	63
10070099	7 G 0.5	6.7	33.6	81
18020099	2 X 0.75	5.4	14.4	45
11030099	3 G 0.75	5.7	21.6	55
18030099	3 X 0.75	5.7	21.6	55
11040099	4 G 0.75	6.2	28.8	66
18040099	4 X 0.75	6.2	28.8	66
11050099	5 G 0.75	6.7	36	79
11070099	7 G 0.75	7.3	50	101
18520099	2 X 1.0	5.7	19.2	53
12030099	3 G 1.0	6	28.8	65
12040099	4 G 1.0	6.5	38.4	79
12050099	5 G 1.0	7.1	48	94
12070099	7 G 1.0	8	67	126
19020099	2 X 1.5	6.3	29	68
13030099	3 G 1.5	6.7	43	84
13040099	4 G 1.5	7.2	58	104
13050099	5 G 1.5	8.1	72	128
13070099	7 G 1.5	8.9	101	166
19520099	2 X 2.5	7.5	48	101
14030099	3 G 2.5	8.1	72	132
14040099	4 G 2.5	8.9	96	163
14050099	5 G 2.5	10	120	200
14070099	7 G 2.5	11.1	168	267

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16