

# H05VVC4V5-K

H05VVC4V5-K (EN 50525-2-51)

H05VVC4V5-K harmonised PVC control cable, oil-resistant, screened, flexible and numbered for various applications, U<sub>0</sub>/U: 300/500 V

EN 50363-4-1 : TM5  
(HAR): H05VVC4V5-K  
EMC  
CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



가 가  
EMC-  
( )

(24.04.2024)

# H05VVC4V5-K

: IEC 60332-1-2  
EN 50363-4-1 : TM5

( . 250 /km, 30 MHz )

EN 50525-2-51

PVC 가  
PVC ,  
가 (RAL 7001) PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	IEC 60228/VDE 0295 class 5
:	: 20 x : 6 x
:	U0/U: 300/500 V
:	2000 V
:	G = GN/YE X = GN/YE
:	: -5°C ~ +70°C : -40°C +70°C

가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).  
가 VAT 가 가 .

	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
H05VVC4V5-K				
0035700	3 G 0.5	8 - 10	47	111.3
0035701	4 G 0.5	8.5 - 10.7	58	132.7
0035702	5 G 0.5	9.3 - 11.6	69	162.7
0035703	7 G 0.5	10.8 - 13.5	86	207.7
0035704	12 G 0.5	13.1 - 16.2	142	295
0035710	3 G 0.75	8.3 - 10.4	55	129.4
0035711	4 G 0.75	9.1 - 11.3	67	163.6
0035712	5 G 0.75	9.7 - 12.1	77.4	188.6
0035713	7 G 0.75	11.5 - 14.3	109	246.9
0035714	12 G 0.75	13.8 - 17.1	166	354.3
0035715	18 G 0.75	16.1 - 19.8	257.3	517
0035716	25 G 0.75	18.7 - 23	318.6	677.8
0035717	34 G 0.75	21.4 - 26.2	409.4	860.6
0035720	3 G 1.0	8.8 - 11	62	144.8
0035721	4 G 1.0	9.4 - 11.7	78.3	180.8
0035722	5 G 1.0	10.3 - 12.8	91	209
0035723	7 G 1.0	12.2 - 15.1	118	273
0035724	12 G 1.0	14.5 - 17.9	198	427.6
0035725	18 G 1.0	16.9 - 20.8	303.6	598.6
0035726	25 G 1.0	19.8 - 24.2	411.9	791.8
0035727	34 G 1.0	22.6 - 27.7	516.3	1,003.9
0035730	3 G 1.5	9.7 - 12.1	83	189.7
0035731	4 G 1.5	10.7 - 13.2	97.8	221.6
0035732	5 G 1.5	11.8 - 14.7	118	261.8
0035733	7 G 1.5	14.1 - 17.4	218	356.7
0035734	12 G 1.5	16.7 - 20.6	309.7	559.4
0035735	18 G 1.5	19.5 - 24	411.4	767.6
0035736	25 G 1.5	22.9 - 28	546.5	1049
0035740	3 G 2.5	11.3 - 14	115	241.5
0035741	4 G 2.5	12.6 - 15.5	163	298.3
0035742	5 G 2.5	13.9 - 17.2	191	363.7
0035743	7 G 2.5	16.5 - 20.3	288.9	487.2
0035744	12 G 2.5	19.8 - 24.3	516.6	743.6

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16