



# ÖLFLEX® TRAIN HT 150 FF 1,8kV

Single-core cable according to EN 50382-2 type FF for high requirements in railway applications

ÖLFLEX® TRAIN HT 150 FF 1,8kV - EN 50382-2 FF , 1,8/3kV / . EN 45545: HL1-HL3

Meets EN 50382-2 type FF and EN 45545-2  
High temperature resistance: -40°C up to +150°C



(29.04.2024)

# ÖLFLEX® TRAIN HT 150 FF 1,8kV

Good chemical resistance please see Appendix T1

For high ambient temperatures

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

가 가

EN / IEC 가 :- EN 60754-1 .- EN 60754-2 가 가 .- EN 60684-2  
 가 .- EN 50305 가 가 .- EN 61034-2 .- EN 60332-1-2 .-  
 EN 60332-3-24 / EN 60332-3-25 / EN 50305 .  
 :- EN 50382-2 - EN 50382-2 - EN 50382-2 - EN 50382-2

EN 50355 , A

EN 50264-3-1 Typ MM  
 EN 45545-2 HL1, HL2, HL3

Insulation: Silicone rubber compound, type EI 111  
 : ( )  
 Outer sheath: Silicone rubber compound, type EM 107  
 :

ETIM 5:	ETIM 5.0 Class-ID: EC000057
:	ETIM 5.0
:	VDE 0295 5/ IEC 60228 5
:	가 가
:	: 3 x
:	: 5 x
:	U <sub>0</sub> /U AC 1.8/3 kV
:	U <sub>m</sub> AC 3,6 kV
:	V <sub>0</sub> DC 2,7 kV
:	6,5 kV AC; 15 kV DC
:	-40°C ~ +150°C

가 VAT 가 가 . ( . ) 가 .  
 : 30 kg or 250 m, 가 가 . (e.g. 1 x 500 m or 5 x 100 m ).



# ÖLFLEX® TRAIN HT 150 FF 1,8kV

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
15382040	1 X 1.5	7.4	14.4	63
15382041	1 X 2.5	7.8	24	76
15382042	1 X 4.0	8.4	38.4	93
15382043	1 X 6.0	8.9	57.6	115
15382044	1 X 10.0	10.2	96	168
15382045	1 X 16.0	11.4	153.6	236
15382046	1 X 25.0	13.4	240	339
15382047	1 X 35.0	14.8	336	432
15382048	1 X 50.0	16.3	480	583
15382049	1 X 70.0	18.3	672	780
15382050	1 X 95.0	20.6	912	1039
15382051	1 X 120.0	22.6	1152	1276
15382052	1 X 150.0	24.2	1440	1539
15382053	1 X 185.0	26.6	1776	1871
15382054	1 X 240.0	29.4	2304	2417

(29.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16