


ÖLFLEX® 127 HSLH

Halogen-free control cable, flexible and inexpensive, with CPR Cca, for building wiring

ÖLFLEX® 127 HSLH - halogen-free control cable, HFFR, flexible for various applications, U₀/U: 300/500V, CPR Cca classified

Cca classified according to CPR

CPR: www.lappkabel.com/cpr



Easy handling and installation due to flexible design

Halogen-free and highly flame-retardant materials reduce the risk of fire propagation, high smoke density and toxic fumes in case of fire

Classified fire behavior according to EU Directive 305/2011 (CPR) with article number selection under www.lappkabel.com/cpr 4kV

(CPR)

T14

가

(24.04.2024)

ÖLFLEX® 127 HSLH

, IEC 60332-1-2
()
IEC 60332-3-22 IEC 60332-3-24 IEC 60332-3-25 ()
IEC 60754-1
(가)
IEC 60754-2 () , 가
IEC 61034-2
Toxicity according to NES 713-3 and EN 50306-1

EN 50525-3-11
EN 50525-2-51

가
:
, (RAL 7001)

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0
ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :
: Black with white numbers acc. to VDE 0293-334
: IEC 60228/VDE 0295 class 5
: : 15 x
: : 4 x
: U0/U: 300/500 V
: 4000 V
: G = GN/YE
: X = GN/YE
: : -5°C ~ +70°C
: : -40°C ~ +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

| Article number | (CORE) / (mm ²) | (mm) | (kg/km) | (kg/km) |
|----------------|-----------------------------|------|---------|---------|
| 1127408 | 2 X 0.75 | 5.5 | 14.4 | 43 |
| 1127409 | 3 G 0.75 | 5.8 | 21.6 | 53 |
| 1127413 | 5 G 0.75 | 6.9 | 36 | 80 |
| 1127415 | 7 G 0.75 | 7.5 | 50.4 | 101 |
| 1127417 | 12 G 0.75 | 10.1 | 86.4 | 181 |
| 1127418 | 18 G 0.75 | 12.0 | 129.6 | 263 |
| 1127420 | 2 X 1.0 | 5.8 | 19.2 | 51 |
| 1127421 | 3 G 1.0 | 6.1 | 28.8 | 63 |
| 1127423 | 4 G 1.0 | 6.6 | 38.4 | 78 |
| 1127425 | 5 G 1.0 | 7.3 | 48 | 96 |
| 1127426 | 7 G 1.0 | 8.1 | 67.2 | 126 |
| 1127427 | 12 G 1.0 | 10.7 | 115.2 | 220 |
| 1127428 | 18 G 1.0 | 12.9 | 172.8 | 325 |
| 1127429 | 2 X 1.5 | 6.4 | 28.8 | 67 |
| 1127430 | 3 G 1.5 | 6.8 | 43.2 | 85 |
| 1127432 | 4 G 1.5 | 7.4 | 57.6 | 106 |
| 1127433 | 5 G 1.5 | 8.3 | 72 | 134 |
| 1127434 | 7 G 1.5 | 9.0 | 100.8 | 172 |
| 1127435 | 12 G 1.5 | 12.2 | 172.8 | 307 |
| 1127436 | 3 G 2.5 | 8.3 | 72 | 133 |
| 1127437 | 4 G 2.5 | 9.0 | 96 | 167 |
| 1127438 | 5 G 2.5 | 10.1 | 120 | 210 |
| 1127440 | 4 G 4.0 | 10.8 | 153.6 | 254 |
| 1127441 | 5 G 4.0 | 12.1 | 192 | 318 |
| 1127442 | 4 G 6.0 | 13.0 | 230.4 | 375 |
| 1127443 | 5 G 6.0 | 14.5 | 288 | 468 |
| 1127445 | 5 G 10.0 | 18.1 | 480 | 757 |
| 1127447 | 5 G 16.0 | 21.2 | 768 | 1112 |
| 1127449 | 5 G 25.0 | 26.4 | 1200 | 1711 |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16