

ÖLFLEX® 191 CY

AWM

ÖLFLEX® 191 - UL/CSA AWM PVC

, UL/CSA: 600V

120 mm²

0,75 mm² 가 : ÖLFLEX® 150 CY

EN 50363-4-1 : TM5



4kV

가

EMC-

()

()

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® 191 CY

가 가

Note: for the use of AWM (Appliance Wiring Material) cables in industrial machinery (USA) according to NFPA 79: please see the catalogue appendix table T29

, IEC 60332-1-2
 UL 1581 §1061
 EN 50363-4-1 : TM5

(. 250 /km, 30 MHz)

UL AWM 21098 2587
 CSA AWM I A/B II A/B
 mm² AWG/kcmil 가 가
 T16 .

가
 PVC
 PVC ,
 가 (RAL 7001) PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	IEC 60228/VDE 0295 class 5
:	: 20 x : 6 x
:	HAR U0/U: 300/500 V UL/CSA: 600 V
:	4000 V
:	G = GN/YE X = GN/YE
:	: -5°C ~+70°C UL/CSA: -5°C ~+90°C Fixed installation: -40°C to +70°C UL/CSA: +90°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths



ÖLFLEX® 191 CY

: 30 kg or 250 m, (e.g. 1 x 600 m or 8 x 75 m).

가 VAT 가 가 .

(25.04.2024)

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0011234	7 G 0.75	10.5	85.9	187
0011202	2 X 1.0	8.4	48	126
0011180	3 G 1.0	8.8	55.8	122
0011181	4 G 1.0	9.6	80.8	157
0011182	5 G 1.0	10.3	89.4	183
0011183	7 G 1.0	11.2	99.9	207
0011184	12 G 1.0	14.6	175.7	342
0011185	18 G 1.0	17	241.7	472
0011186	25 G 1.0	20.1	341.7	648
0011302	2 X 1.5	9	64.7	156
0011187	3 G 1.5	9.6	89.1	166
0011188	4 G 1.5	10.3	96.6	191
0011189	5 G 1.5	11.3	111.2	222
0011190	7 G 1.5	12.1	145.2	270
0011191	12 G 1.5	16.1	257	464
0011192	18 G 1.5	18.7	382.8	679
0011193	25 G 1.5	23	546.2	952
0011194	3 G 2.5	10.8	111.1	221
0011195	4 G 2.5	11.4	140.6	269
0011196	5 G 2.5	12.9	167.3	325
0011197	7 G 2.5	14.1	240	421
30010542	12 G 2.5	17.9	414.9	769
30010543	18 G 2.5	22	626.1	1102
30010544	4 G 4.0	13.6	236.7	462
30010545	5 G 4.0	14.9	277.8	535
30010546	7 G 4.0	16.2	393.4	735
30010548	4 G 6.0	15.8	317.1	574
3023130	5 G 6.0	17.3	413.7	737
30010547	7 G 6.0	18.8	563.8	950
3023131	4 G 10.0	19.5	550.4	946
30010639	4 G 16.0	24.7	819.1	1189
3023132	4 G 25.0	28.7	1165	1692
30010928	4 G 35.0	32	1683	2700
3026535	4 G 50.0	39.7	2342	3362

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® 191 CY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
3025946	4 G 70.0	44.8	3229	4490
3025947	4 G 95.0	50	4010	5540
3026536	4 G 120.0	55.4	5012	6960

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16