



ÖLFLEX® CLASSIC 100 H

ÖLFLEX® CLASSIC 100 H - , HFFR
CPR, 450/750V

CPR: www.lappkabel.com/cpr



가

(23.04.2024)

ÖLFLEX® CLASSIC 100 H

WTG() , 가

, IEC 60332-1-2
()
IEC 60332-3-24 IEC 60332-3-25 () , -
IEC 60754-1
(가)
IEC 60754-2 () , 가
IEC 61034-2
EN 50363-4-1(TM5)
UL OIL RES I UL OIL RES II
EN 50396

IEC 60227-5 EN 50525-2-51
EN 50525-3-11

가
:
, (RAL 7001)

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	VDE 0293-308 , T9
:	IEC 60228/VDE 0295 class 5
WTG :	TW-0 & TW-2, T0
:	: 15 x
	: 4 x
:	U0/U: 450/750 VAC
	:
	U0/U: 600/1000 V
:	4000 V
:	G = GN/YE
	X = GN/YE
:	: -30 °C ~ +70 °C
	: -40°C +80°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).



ÖLFLEX® CLASSIC 100 H

: 4G50 500 m; 4G120 400 m

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 100 H

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
0014150	2 X 1.5	7.6	28.8	91
0014151	3 G 1.5	8.3	43.2	114
0014152	4 G 1.5	9	57.6	140
0014153	5 G 1.5	10.1	72	176
0014156	2 X 2.5	9	48	133
0014157	3 G 2.5	9.7	72	167
0014158	4 G 2.5	10.8	96	207
0014159	5 G 2.5	11.9	120	260
0014162	3 G 4.0	11.4	115.2	240
0014163	4 G 4.0	12.7	153.6	303
0014164	5 G 4.0	13.9	192	372
0014166	3 G 6.0	12.7	172.8	320
0014167	4 G 6.0	13.9	230.4	400
0014168	5 G 6.0	15.8	288	510
0014170	4 G 10.0	17.9	384	662
0014171	5 G 10.0	19.9	480	826
0014173	4 G 16.0	20.7	614.4	957
0014174	5 G 16.0	23	768	1193
0014176	4 G 25.0	25.4	960	1480
0014177	5 G 25.0	28.5	1200	1860
0014179	4 G 35.0	28.8	1344	1985
0014180	5 G 35.0	32.3	1680	2490
0014182	4 G 50.0	35	1920	2830
0014184	4 G 70.0	40	2688	3890
0014186	4 G 95.0	46	3648	5110
0014188	4 G 120.0	51	4608	6315

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16