

# ÖLFLEX® 191

AWM

ÖLFLEX® 191 - UL/CSA AWM PVC

, UL/CSA: 600V

120 mm<sup>2</sup>

0,5 0,75 mm<sup>2</sup> 가 : ÖLFLEX® 150

EN 50363-4-1 : TM5



4kV

가 가

Note: for the use of AWM (Appliance Wiring Material) cables in industrial machinery (USA) according to NFPA 79: please see the catalogue appendix table T29

(23.04.2024)

# ÖLFLEX® 191

, IEC 60332-1-2  
 UL 1581 §1061  
 EN 50363-4-1 : TM5

UL AWM 21098 2587  
 CSA AWM I A/B II A/B  
 mm<sup>2</sup> AWG/kcmil T16

PVC  
 PVC  
 가 (RAL 7001) PVC

ETIM 5: ETIM 5.0 Class-ID: EC000104  
 ETIM 5.0  
 ETIM 6: ETIM 6.0 Class-ID: EC000104  
 ETIM 6.0 Class :  
 : Black with white numbers acc. to VDE 0293-334  
 : IEC 60228/VDE 0295 class 5  
 : : 15 x  
 : : 4 x  
 : HAR U0/U: 300/500 V  
 UL/CSA: 600 V  
 : 4000 V  
 : G = GN/YE  
 : X = GN/YE  
 : : -5°C ~+70°C  
 UL/CSA: -5°C ~+90°C  
 Fixed installation: -40°C to +70°C  
 UL/CSA: +90°C

가 가 ( ) 가  
 www.lappkabel.de/en/cable-standradlengths  
 : 30 kg or 250 m,  
 . (e.g. 1 x 600 m or 8 x 75 m ).  
 가 VAT 가 가

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
0011222	7 G 0.75	8.3	50.4	116
0011223	9 G 0.75	10.5	64.8	152
0011224	12 G 0.75	11.2	86.4	194
0011113	3 G 1.0	6.7	28.8	66
0011114	4 G 1.0	7.2	38.4	81
0011115	5 G 1.0	8.1	48	95
0011116	7 G 1.0	8.9	67.2	125
0011117	12 G 1.0	12	115.2	211
0011118	18 G 1.0	14.4	172.8	309
0011119	25 G 1.0	17.3	240	413
0011136	2 X 1.5	6.9	28.8	74
0011137	3 G 1.5	7.3	44	91
0011138	4 G 1.5	8.2	58	112
0011139	5 G 1.5	9	72	136
0011140	7 G 1.5	10	101	179
0011125	9 G 1.5	12.6	129.6	230
0011142	12 G 1.5	13.4	173	313
0011143	18 G 1.5	16.1	260	444
0011144	25 G 1.5	19.5	360	620
0011150	3 G 2.5	8.4	72	138
0011151	4 G 2.5	9.1	96	182
0011152	5 G 2.5	10.2	120	216
0011153	7 G 2.5	11.3	168	286
0011160	3 G 4.0	9.9	115.2	202
0011161	4 G 4.0	10.8	154	245
0011162	5 G 4.0	12.1	192	310
0011167	7 G 4.0	13.4	268.8	470
0011165	4 G 6.0	13	231	398
0011166	5 G 6.0	14.5	288	479
0011169	4 G 10.0	16.5	384	559
0011170	5 G 10.0	18.4	480	782
0011172	4 G 16.0	22.1	615	904
0011173	5 G 16.0	24.3	768	1171
0011175	4 G 25.0	25.2	960	1299

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



ÖLFLEX® 191

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
0011176	5 G 25.0	28	1200	1640
0011178	4 G 35.0	28.1	1344	2119
0011179	5 G 35.0	31.5	1680	2606
0011205	4 G 50.0	35.7	1920	2898
0011206	4 G 70.0	43	2688	4052
0011207	4 G 95.0	47.2	3648	5430
0011208	4 G 120.0	51	4608	6290

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16