

ÖLFLEX® SF

가 H05VV-F

ÖLFLEX® SF-H05VV-F , U
ø/U: 300/500V HAR PVC

EN 50396



가 ,
H05VV-F

: IEC 60332-1-2

EN 50396

EN 50525-2-11 H05VV-F,
6 : EN 50525-2-11

PVC 0.07mm
- 가 (RAL 2003) PVC

(25.04.2024)

ÖLFLEX® SF

ETIM 5:	ETIM 5.0 Class-ID: EC001578
	ETIM 5.0 Class 가
ETIM 6:	ETIM 6.0 Class-ID: EC001578
	ETIM 6.0 Class :
:	VDE 0293-308 , T9
	6 :
:	(0.07 mm)
:	: 10 x
	: 4 x
:	U0/U: 300/500 V
:	3000 V
:	G = GN/YE
	X = GN/YE
:	: -15°C ~ +60°C

 , 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



ÖLFLEX® SF

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SF				
0027590	2 X 0.75	6.4	14.9	50
0027591	3 G 0.75	7	22.3	60
00275923	4 G 0.75	7.7	29.7	73
00275933	5 G 0.75	8.7	37.1	88
0027600	2 X 1.0	6.8	20.1	74
0027601	3 G 1.0	7.4	30.2	87
00276033	5 G 1.0	9.2	50.8	130
0027701	3 G 1.5	8.7	44.8	116
00277023	4 G 1.5	9.9	61	166
00277033	5 G 1.5	11.1	72	184

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16