


# ÖLFLEX® CLASSIC 115 CH

Screened halogen-free control cable, oil resistant, very flexible and space-saving

ÖLFLEX® CLASSIC 115 CH - halogen-free control cable, HFFR, oil-resistant, screened, cold-resistant and space-saving for various applications, U<sub>0</sub>/U: 300/500V

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

가 ,



가

(25.04.2024)



# ÖLFLEX® CLASSIC 115 CH

Halogen-free and highly flame-retardant materials reduce the risk of fire propagation, high smoke density and toxic fumes in case of fire

가  
(CPR) T14  
Considering the temperature range, a temporary outdoor use is possible

, IEC 60332-1-2  
( )  
IEC 60332-3-24 IEC 60332-3-25 ( ) , -  
UL Cable Flame Test  
IEC 60754-1  
( 가 )  
IEC 60754-2 ( ) , 가  
IEC 61034-2  
EN 50363-4-1(TM5)  
UL OIL RES I UL OIL RES II  
ISO 4892-2UV UV  
EN 50396

UL AWM 21089  
EN 50525-3-11  
EN 50525-2-51

가  
:  
:  
, (RAL 7001)

ETIM 5: ETIM 5.0 Class-ID: EC000104  
ETIM 5.0  
ETIM 6: ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :  
: Black with white numbers acc. to VDE 0293-334  
: IEC 60228/VDE 0295 class 5  
: : 15 x  
: : 6 x  
: U0/U: 300/500 V  
UL: 600 V



# ÖLFLEX® CLASSIC 115 CH

: 4000 V  
 : G = GN/YE  
 : X = GN/YE  
 : : -30~70°C(UL: 75°C)  
 : -40~80°C(UL: 75°C)

, 가 가 . ( . ) 가 .  
 : [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 30 kg or 250 m,  
 : (e.g. 1 x 500 m or 5 x 100 m ).  
 : 4G50 500 m

가 VAT 가 가 .

(25.04.2024)

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
10036001	2 X 0.5	5.9	36	56
10036002	3 G 0.5	6.2	43	67
10036003	3 X 0.5	6.2	43	67
10036004	4 G 0.5	6.6	49	78
10036005	4 X 0.5	6.6	49	78
10036006	5 G 0.5	7.1	57	91
10036007	7 G 0.5	7.7	69	110
10036008	12 G 0.5	10.1	104	177
10036009	2 X 0.75	6.3	43	65
10036010	3 G 0.75	6.6	52	77
10036011	3 X 0.75	6.6	52	77
10036012	4 G 0.75	7.1	61	92
10036013	4 X 0.75	7.1	61	92
10036014	5 G 0.75	7.9	72	111
10036015	5 X 0.75	7.9	72	111
10036016	7 G 0.75	8.5	89	138
10036017	7 X 0.75	8.5	89	138
10036018	12 G 0.75	11.1	138	220
10036019	18 G 0.75	13.0	211	312
10036020	25 G 0.75	15.1	280	417
10036021	2 X 1.0	6.6	51	73
10036022	3 G 1.0	6.9	62	89
10036023	3 X 1.0	6.9	62	89
10036024	4 G 1.0	7.4	74	107
10036025	4 X 1.0	7.4	74	107
10036026	5 G 1.0	8.3	88	131
10036027	7 G 1.0	8.9	112	159
10036028	12 G 1.0	11.7	185	263
10036029	18 G 1.0	14.1	268	378
10036030	25 G 1.0	16.2	354	508
10036031	41 G 1.0	20.6	547	834
10036032	2 X 1.5	7.2	65	87
10036033	3 G 1.5	7.6	82	108
10036034	3 X 1.5	7.6	82	108

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® CLASSIC 115 CH

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
10036035	4 G 1.5	8.4	100	136
10036036	5 G 1.5	9.1	119	162
10036037	7 G 1.5	10.0	154	204
10036038	12 G 1.5	13.4	268	340
10036039	18 G 1.5	15.8	373	492
10036040	25 G 1.5	18.2	530	654
10036041	3 G 2.5	9.1	118	157
10036042	4 G 2.5	10.0	147	198
10036043	5 G 2.5	11.1	176	245
10036044	7 G 2.5	12.0	253	307
10036045	12 G 2.5	16.3	385	524
10036046	4 G 4.0	11.8	248	284
10036047	5 G 4.0	13.3	269	368
10036048	7 G 4.0	14.6	371	448
10036049	4 G 6.0	14.2	343	406
10036050	5 G 6.0	15.5	441	522
10036051	7 G 6.0	17.0	510	637
10036052	4 G 10.0	17.2	495	656
10036053	5 G 10.0	19.5	592	865
10036054	4 G 16.0	20.2	736	972
10036055	5 G 16.0	22.6	895	1249
10036056	4 G 25.0	25.1	1129	1482
10036057	5 G 25.0	28.0	1400	1906
10036058	4 G 35.0	28.2	1546	1971
10036059	5 G 35.0	31.4	1912	2529
10036060	4 G 50.0	34.0	2186	2713
10036061	4 G 70.0	39.0	3011	3709

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16