

ÖLFLEX® CLASSIC 128 H BK 0,6/1 kV

가 , 0.6/1kV

ÖLFLEX® CLASSIC 128 H BK 0.6/1kV, / , HFFR , 5,

ISO 4892-2UV UV



CE UK CA



Easy handling and installation due to flexible design

가

(24.04.2024)

ÖLFLEX® CLASSIC 128 H BK 0,6/1 kV

, IEC 60332-1-2
 ()
 IEC 60332-3-24 IEC 60332-3-25 () , -
 IEC 60754-1
 (가)
 IEC 60754-2 () , 가
 IEC 61034-2
 ISO 4892-2UV UV
 EN 50396

EN 50525-3-11

가
 :

ETIM 5:	ETIM 5.0 Class-ID: EC000057
	ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000057
	ETIM 6.0 Class :
:	5 : VDE 0293-308 . T9
	6 :
:	VDE 0295 5/ IEC 60228 5
	가 가
:	: 15 x
	: 4 x
:	U0/U: 600/1000 V
:	4000 V
:	G = GN/YE
	X = GN/YE
:	: -5°C ~ +70°C
	: -40°C bis +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

ÖLFLEX® CLASSIC 128 H BK 0,6/1 kV

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1123520	2 X 1.0	7.4	19.2	76
1123521	3 G 1.0	7.8	28.8	101
1123522	4 G 1.0	8.4	38.4	120
1123523	5 G 1.0	9.2	48	143
1123524	7 G 1.0	9.9	67.2	179
1123525	12 G 1.0	12.8	115.2	283
1123528	2 X 1.5	8.4	28.8	112
1123529	3 G 1.5	8.9	43.2	135
1123530	4 G 1.5	9.6	57.6	163
1123531	5 G 1.5	10.5	72	196
1123532	7 G 1.5	11.4	100.8	253
1123533	12 G 1.5	15.1	172.8	396
1123534	18 G 1.5	18.0	259.2	589
1123535	25 G 1.5	21.1	360	801
1123537	3 G 2.5	10.1	72	189
1123538	4 G 2.5	11.0	96	232
1123539	5 G 2.5	12.1	120	279
1123541	12 G 2.5	17.9	288	603
1123544	3 G 4.0	11.4	115.2	260
1123545	4 G 4.0	12.5	153.6	322
1123546	5 G 4.0	13.7	192	387
1123548	4 G 6.0	13.9	230.4	431
1123549	5 G 6.0	15.8	288	533
1123550	4 G 10.0	17.9	384	734
1123553	4 G 25.0	25.2	960	1617

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CLASSIC 128 H BK 0,6/1 kV



(24.04.2024)