

SILVYN® EMC AS-CU

SILVYN® EMC AS-CU

EMC

가



EMC

-

/

가

EN 50289-1-6

30MHz

80dB

가

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EMC AS-CU

VDE

ETIM 5:

ETIM 5.0 Class-ID: EC001179

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001179

ETIM 6.0 Class :

:

IEC EN 61386-23

:

:

:

-50°C ~+250°C

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EMC AS-CU

	()	ID x OD mm	(mm)	SILVYN® MSK-M	SILVYN® US-M	SILVYN® US	PU ring (m)
SILVYN® EMC AS-CU							
64400500	10	7 x 10	28	12 x 1,5	10 x 1,0	7	50
64400501	14	10 x 14	34	16 x 1,5	12 x 1,5	9	50
64400502	17	13 x 17	40	20 x 1,5	16 x 1,5	11	50
64400504	21	17 x 21	50	25 x 1,5	20 x 1,5	16	50
64400505	27	22 x 27	63	32 x 1,5	25 x 1,5	21	50
64400506	36	29 x 36	85	40 x 1,5	32 x 1,5	29	25
64400507	45	38 x 45	100	50 x 1,5	40 x 1,5	36	25
64400508	56	49 x 56	135	63 x 1,5	50 x 1,5	48	25

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16