

# ÖLFLEX® CLASSIC 135 CH

ÖLFLEX® CLASSIC 135 CH - , HFFR, , U  
ø/U: 300/500V

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

A temporary outdoor use is possible



Easy handling and installation due to flexible design

Note: for the use of AWM (Appliance Wiring Material) cables in industrial machinery (USA) according to NFPA 79: please see the catalogue appendix table T29

EMC-

가

(23.04.2024)

# ÖLFLEX® CLASSIC 135 CH

( )  
Considering the temperature range, a temporary outdoor use is possible

( ) , IEC 60332-1-2  
( )  
IEC 60332-3-22 IEC 60332-3-24 IEC 60332-3-25 ( )  
IEC 60754-1  
( ) 가 )  
IEC 60754-2 ( ) , 가  
IEC 61034-2

UL AWM style 21217  
EN 50525-3-11  
EN 50525-2-51  
DNV GL certificate no. TAE00002RK

가  
:  
.  
, (RAL 7001)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	IEC 60228/VDE 0295 class 5
:	: 20 x : 6 x
:	U0/U: 300/500 V UL: 600 V
:	Core/core: 4000 V Core/screen: 2000 V
:	G = GN/YE X = GN/YE
:	: -25°C ~+70°C (UL:+75°C) : -40~80°C(UL: 75°C)

가 가 . ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m ).



## ÖLFLEX® CLASSIC 135 CH

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® CLASSIC 135 CH

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 135 CH				
1123200	2 X 0.5	5.9	36	51
1123201	3 G 0.5	6.2	43	61
1123202	3 X 0.5	6.2	43	61
1123203	4 G 0.5	6.6	49	72
1123204	4 X 0.5	6.6	49	72
1123205	5 G 0.5	7.1	57	85
1123206	5 X 0.5	7.1	57	85
1123208	7 G 0.5	7.7	69	103
1123209	7 X 0.5	7.7	69	103
1123213	12 G 0.5	10.1	104	165
1123217	18 G 0.5	11.8	141	236
1123220	25 G 0.5	13.7	224	324
1123232	2 X 0.75	6.3	43	60
1123233	3 G 0.75	6.6	52	77
1123234	3 X 0.75	6.6	52	77
1123235	4 G 0.75	7.1	61	87
1123236	4 X 0.75	7.1	61	87
1123237	5 G 0.75	7.9	72	106
1123238	5 X 0.75	7.9	72	106
1123241	7 G 0.75	8.5	89	129
1123242	7 X 0.75	8.5	89	129
1123247	12 G 0.75	11.1	138	211
1123248	12 X 0.75	11.1	138	211
1123251	18 G 0.75	13	211	307
1123254	25 G 0.75	15.1	280	413
1123266	2 X 1.0	6.6	51	79
1123267	3 G 1.0	6.9	62	88
1123268	3 X 1.0	6.9	62	88
1123269	4 G 1.0	7.4	74	106
1123270	4 X 1.0	7.4	74	106
1123271	5 G 1.0	8.3	88	124
1123272	5 X 1.0	8.3	88	124
1123274	7 G 1.0	8.9	112	155

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1123275	7 X 1.0	8.9	112	155
1123280	12 G 1.0	11.7	185	250
1123281	12 X 1.0	11.7	185	250
1123284	18 G 1.0	14.1	268	368
1123290	25 G 1.0	16.2	354	493
1123291	25 X 1.0	16.2	354	493
1123306	2 X 1.5	7.2	65	91
1123307	3 G 1.5	7.6	82	112
1123308	3 X 1.5	7.6	82	112
1123309	4 G 1.5	8.4	100	141
1123310	4 X 1.5	8.4	100	141
1123311	5 G 1.5	9.1	119	161
1123312	5 X 1.5	9.1	119	161
1123314	7 G 1.5	10	154	206
1123315	7 X 1.5	10	154	206
1123320	12 G 1.5	13.4	268	355
1123324	18 G 1.5	15.8	373	517
1123328	25 G 1.5	18.2	530	705
1123339	2 X 2.5	8.6	96	128
1123340	3 G 2.5	9.1	118	157
1123342	4 G 2.5	10	147	201
1123344	5 G 2.5	11.1	176	248
1123346	7 G 2.5	12	253	313
1123349	12 G 2.5	16.3	385	524
1123359	3 G 4.0	10.6	178	231
1123360	4 G 4.0	11.8	248	291
1123361	5 G 4.0	13.3	269	361
1123362	7 G 4.0	14.6	371	468
1123366	3 G 6.0	12.7	240	318
1123367	4 G 6.0	14.2	343	437
1123368	5 G 6.0	15.5	441	510
1123369	7 G 6.0	17	510	662
1123372	4 G 10.0	17.2	495	685
1123373	5 G 10.0	19.5	592	824

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ÖLFLEX® CLASSIC 135 CH

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1123374	7 G 10.0	21.4	820	1067
1123377	4 G 16.0	20.2	736	1036
1123378	5 G 16.0	22.6	895	1285
1123381	4 G 25.0	25.1	1129	1663
1123382	5 G 25.0	28	1400	1976
1123385	4 G 35.0	28.2	1546	2052

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16