

SILVYN® MSK-M BRUSH

SILVYN® MSK-M BRUSHED - EMC

BRUSH
360°



**CE UK
CA**



SKINTOP®

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® MSK-M BRUSH

,

EMC-

SILVYN® SKINTOP®

, SKINTOP®

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

:

:

: CR/NBR

: TPE

EMC :

가:

Cable: IP 68

Conduit:

IP 40 with SILVYN® AS, EDU-AS, EMC AS-CU

IP 65 with SILVYN® AS-P

:

-30°C ~ +100°C

가 VAT 가 가 .

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® MSK-M BRUSH

		Clamping range in mm	(mm)	OØ (mm)	/ PU
SILVYN® AS SILVYN® MSK-M BRUSH					
55506020	25 x 1.5	9.0 - 17.0	14.5	21	10
55506021	32 x 1.5	11.0 - 21.0	19.5	27	1
55506022	40 x 1.5	19.0 - 28.0	26.5	36	1
55506023	50 x 1.5	27.0 - 35.0	36	45	1
55506024	63 x 1.5	34.0 - 45.0	45.5	56	1
SILVYN®AS-P/EDU-AS/EMC AS-CU SILVYN®MSK-M BRUSH					
55506025	25 x 1.5	9.0 - 17.0	14.5	21	10
55506026	32 x 1.5	11.0 - 21.0	19.5	27	1
55506027	40 x 1.5	19.0 - 28.0	26.5	36	1
55506028	50 x 1.5	27.0 - 35.0	36	45	1
55506029	63 x 1.5	34.0 - 45.0	45.5	56	1