



ÖLFLEX® EB

IEC 60079-14/EN 60079-14/VDE 0165-1

ÖLFLEX® EB - 가 PVC ,U
0/U: 300/500V

CPR: www.lappkabel.com/cpr 'i'

ISO 4892-2UV UV



IEC 60079-14:2013/EN 60079-14:2014/VDE 0165-1:2014, 16.2.2 (i-)

ISO 4892-2UV UV
: IEC 60332-1-2

EN 50525-2-51

PVC LAPP P8/1 가

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

ÖLFLEX® EB

RAL 5015 PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	Black with white numbers acc. to VDE 0293-334
:	Core/core approx. 140 nF/km
:	approx. 0.52 mH/km
:	IEC 60228/VDE 0295 class 5
:	: 15 x
:	: 4 x
:	U0/U: 300/500 V
:	Core/core: 3000 V
:	: -5°C ~ +70°C
:	: -40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



ÖLFLEX® EB

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® EB GN/YE				
0012420	2 X 0.75	5.4	14.7	50
0012421	3 X 0.75	5.7	22.1	60
0012430	4 X 0.75	6.2	29.4	81
0012422	5 X 0.75	6.7	36.8	88
0012423	7 X 0.75	7.3	51.5	115
0012425	12 X 0.75	9.9	88.2	185
0012427	18 X 0.75	11.7	132.3	282
0012429	25 X 0.75	13.8	183.8	393
0012440	2 X 1.0	5.7	19.7	57
0012441	3 X 1.0	6	29.6	73
0012443	5 X 1.0	7.1	49.4	105
0012444	7 X 1.0	8	69.1	138
0012446	12 X 1.0	10.5	118.4	231
0012448	18 X 1.0	12.7	177.7	331
0012401	2 X 1.5	6.3	29	80
0012402	3 X 1.5	6.7	43	105
0012403	4 X 1.5	7.2	58	125
0012404	5 X 1.5	8.1	72	139
ÖLFLEX® EB GN/YE				
0012501	3 G 1.5	6.7	43	105
0012502	4 G 1.5	7.2	58	125
0012503	5 G 1.5	8.1	72	139
0012504	7 G 1.5	8.9	101	180
0012505	12 G 1.5	12	173	339
0012506	18 G 1.5	14.4	259	513
0012507	25 G 1.5	16.9	360	698

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16