

FIPLOCK® ONE ST-PG

FIPLOCK® PA6 / PA12

FIPLOCK[®] ONE ST-PG



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FIPLOCK® ONE ST-PG



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176
ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176
ETIM 6.0 Class :

:

IEC EN 61386-23
EN 45545-2 HL3

:

(RAL 7005) (RAL 9005), UV

:

PA 6

가:

UL 94V-0
IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)



FIPLOCK® ONE ST-PG

가 VAT 가 가 .

(24.04.2024)

FIPLLOCK® ONE ST-PG

	PG	Clamping range in mm	SW 1/2 mm	(thread) (mm)	FIPLLOCK® PA6 / PA12		/ PU
61804836	9	3.5 - 8.0	19.0 / 20.0	8	10		10
61804837	9	3.5 - 8.0	19.0 / 22.0	8	12		10
61804838	11	4.0 - 10.0	22.0 / 22.0	8	12		10
61804839	13.5	6.0 - 12.0	24.0 / 22.0	9	12		10
61804841	13.5	6.0 - 12.0	24.0 / 27.0	9	17		10
61804842	16	9.0 - 14.0	27.0 / 27.0	10	17		10
61804843	16	9.0 - 14.0	27.0 / 36.0	10	23		6
61804844	21	13.0 - 18.0	33.0 / 36.0	11	23		6
61804845	29	14.0 - 25.0	42.0 / 41.0	11	29		6
61804846	36	24.0 - 32.0	53.0 / 52.0	13	36		4
61804847	48	39.0 - 44.0	65.0 / 65.0	14	48		4
61804848	9	3.5 - 8.0	19.0 / 20.0	8	10		10
61804849	9	3.5 - 8.0	19.0 / 22.0	8	12		10
61804851	11	4.0 - 10.0	22.0 / 22.0	8	12		10
61804852	13.5	6.0 - 12.0	24.0 / 22.0	9	12		10
61804853	13.5	6.0 - 12.0	24.0 / 27.0	9	17		10
61804854	16	9.0 - 14.0	27.0 / 27.0	10	17		10
61804855	16	9.0 - 14.0	27.0 / 36.0	10	23		6
61804856	21	13.0 - 18.0	33.0 / 36.0	11	23		6
61804857	29	14.0 - 25.0	42.0 / 41.0	11	29		6
61804858	36	24.0 - 32.0	53.0 / 52.0	13	36		4
61804859	48	39.0 - 44.0	65.0 / 65.0	14	48		4

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16